


△ PART NO. AND CH. CODE	R ₁	R ₂	W ₁	W ₂	△H ₁	△H ₂	C	D	WIRE SIZE (mm ²)
7116-4140-02	0.70	1.90	3.10	6.40	△(3.10)	△(5.70)	4.00	10.50	△ 0.5~1.25 OR EQUIVALENT
7116-4141-02	0.95	2.20	4.00	7.30	△(4.00)	△(6.50)	4.00	10.50	△ 1.4~2.5 OR EQUIVALENT
7116-4142-02	1.35	2.70	5.00	8.30	△(4.80)	△(7.00)	4.50	11.00	△ 3.0~4.0 OR EQUIVALENT
△ 7116-4143-02	1.35	2.90	5.60	9.10	△(5.85)	△(7.95)	4.50	11.00	5.0 FOR ESB-MIL-123-A

注記


1. 嵌合相手品番 : 7114-4140-02 ETC.
△ 2. 7116-4143-02においての通電流値は、4.0 mm²電線相当以下とする。



NOTES

1. MATING PART NO. : 7114-4140-02 ETC.
△ 2. CURRENT FOR 7116-4143-02 SHALL BE THE
CURRENT FOR 4.0 mm² WIRE OR UNDER.



SEC. A-A (5/1) SEC. B-B (5/1)



APPLICABLE WIRE SIZE MARK
 (7116-4140-02)
 (7116-4141-02)
 (7116-4142-02)
 △ (7116-4143-02)

△	03.07.10	CHANGED WIRE SIZE	C03-X451	K.0
△	99.10.21	CHANGED DIMENSION ETC.	C99-M581	M.K
△	98.07.24	ADDED PART NO. ETC.	C98-M234	Y.U
△	98.04.17	CHANGED FORM	C98-L496	H.T
△	96.08.01	NEW	C96-M174	H.K
LET	DATE	REVISION RECORD	NO.	CHKD
GENERAL TOLERANCE				
	10MAX	50MAX	100MAX	250MAX
A	±0.15	±0.2	±0.3	±0.5
B	±0.2	±0.3	±0.55	±1.4
C	±0.3	±0.5	±0.8	±1.4
SPECIFIED		MASS		
		g		

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.	
OFFICE		TRIAL PART NO.			
VENDOR NO.					
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	96.08.01	mm	2/1	3
APPROVED	CHECKED	DESIGN	DRAWN		
Y. OHKUBO	Y. OHKUBO	Y. OHKUBO	Y. OHKUBO		

NAME △ 6.3 SYSTEM SEALED CONNECTOR		FEMALE TERMINAL	
MATERIAL: COPPER ALLOY t=0.40		TREAT. & FIN.	
SPEC. (TIN PLATING)			
PART NO.	7116-4140-02	CH. CODE	ETC.
DWG NO.	7116-4140-02	SET DWG NO.	
YAZAKI CORPORATION			