


23-925-0000-90

Insertion Loss: $.05 \sqrt{\text{Frequency}}$



LTR	DESCRIPTION	DATE	APPR.	DRAWN LMW	CHECKED	USED ON 23-925-0000-90		 SRI CONNECTOR GAGE CO. 3950 DOW ROAD MELBOURNE FL. 32934																	
—	REL	12/02		APPR.	SCALE																				
				UNLESS OTHERWISE SPECIFIED: 1. REMOVE ALL BURRS 2. BREAK ALL CORNERS & EDGES .005 R. MAX 3. CHAMFER 1st & LAST THREADS 45° 4. SURFACE FINISHED 32✓ UNLESS OTHERWISE SPECIFIED. 5. DIAMETERS ON COMMON CENTERS TO BE CONCENTRIC WITHIN .004 T.I.R. 6. ALL DIMENSIONS ARE AFTER PLATING.		MATERIAL		TITLE 3.5mm JACK TO 2.9mm JACK																	
						FINISH																			
						DIMENSIONS ARE IN INCHES TOLERANCES		SIZE A	FSCM NO. OHMO1	SHEET 1	DWG. NO. 23-925-0000-90														
								<table><tr><th colspan="2">DECIMALS</th><th>FRACTIONAL</th><th colspan="2">ANGULAR</th></tr><tr><td>.X</td><td>±.030</td><td rowspan="3">± 1/64</td><td>.X°</td><td>±1°0'</td></tr><tr><td>.XX</td><td>±.010</td><td>.X°X'</td><td>±15'</td></tr><tr><td>.XXX</td><td>±.005</td><td></td><td></td></tr></table>	DECIMALS		FRACTIONAL	ANGULAR		.X	±.030	± 1/64	.X°	±1°0'	.XX	±.010	.X°X'	±15'	.XXX	±.005	
DECIMALS		FRACTIONAL	ANGULAR																						
.X	±.030	± 1/64	.X°	±1°0'																					
.XX	±.010		.X°X'	±15'																					
.XXX	±.005																								