

This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.

MATERIALS:

- SST 303, PER ASTM A582.
- BERYLLIUM COPPER ASTM B196.
- OXIDE-NORYL (TM). MIL-P-46129.



FINISH:

- CENTER CONDUCTORS AND SOLDER COMPONENTS SHALL BE GOLD PLATED PER MIL-DTL-45204D TYPE II, CLASS 1 OVER NICKEL PLATE PER QQ-N-290.
- BODY AND BODY COMPONENTS SHALL BE PASSIVATED PER AMS2700.

PERFORMANCE:

- FREQUENCY: DC-40GHz
- VSWR: 1.25 MAX.
- INSERTION LOSS: .32 dB
- OPERATING TEMP: -55°C TO 100°C
- IMPEDANCE: 50Ohms Nom.

REV	DESCRIPTION	DATE	APPD
-	REL	04/03	LMW
A	ECO-13227	11/24/20	LA



MATERIAL	DO NOT SCALE DRAWING	DRAWN LMW	DATE 04/03	 Winchester Interconnect _{LLC}	68 Water St Norwalk, CT 06854	
	UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONS: ± 1/64 .XX : ± .01 .XXX: ± .005 ANGLES: ± 2°	ENG APPR.	DATE			
		MFG APPR.	DATE			
		OTHER APPR.	DATE			
COMMENTS:	THIRD ANGLE PROJECTION 	TITLE: 2.9 MM PLUG TO 2.9 MM JACK ADAPTER			REV A	
surface area: sq inch		SIZE B	DWG. NO. 24-925-0000-90	PER ASME Y14.5M-1994		
		SCALE: 3.65:1				SHEET 1 OF 1
		weight: lbs				

CUSTOMER OUTLINE DRAWING