

This document, including the design, configuration and mechanical features revealed herein are the sole, confidential and proprietary property of Winchester Interconnect. Reproduction or use thereof, in whole or part, is prohibited without the prior written consent of Winchester Interconnect.


REV	DESCRIPTION	DATE	APPROVED
C	ECO-N30248	09/30/24	FUH

B

B

A

A





Front Panel Jack Only Clearance
W/O Latch Feature

Single Panel-Latch Clearance
Panel Thickness 0.062 inch

CATALOG P/N: 310188S



DRAWN FUH	DATE 09/30/2024	 Winchester Interconnect.		185 Plains Rd, Suite 100W Milford, CT 06461			
APPR. DCAM	DATE 09/30/2024						
APPR. XXX	DATE XX/XX/XX	TITLE:					
APPR. XXX	DATE XX/XX/XX	MODULAR COUPLER JACK (8P8C SHIELDED)					
THIRD ANGLE PROJECTION 		SIZE A SH 1 OF 1	DWG. NO. SD310188S		REV C		

MATERIALS:
SHIELDED: STAINLESS STEEL.
PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0.
CONTACTS: 0.35MM THICKNESS PHOSPHOR BRONZE
PLATING: GOLD PLATING OVER NICKEL IN CONTACT.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MM

TOLERANCES:
.X: ± 0.38
.XX: ± 0.25
.XXX: ± 0.10
ANGLES: $\pm 3^\circ$