




REV	ECN	DESCRIPTION	APP'D
-	7434	RELEASE	<i>1/5/15</i>



1. MATERIALS:
- A. INSULATOR - POLYETHERMIDE, COLOR: GREEN.
 - B. CONTACTS - BERYLLIUM COPPER HEAT TREATED.
PLATING: MATING AREA - 50 MICROINCH GOLD PER MIL-G-45204
OVER 30 MICROINCH NICKEL PER QQ-N-290.
SOLDER TAILS - 100 MICROINCH TIN-LEAD PER MIL-P-51728.
 - C. HARDWARE -
STUD AND NUT - CORROSION RESISTANT STEEL TYPE 300
OR A268, PASSIVATE PER QQ-P-35.
WASHER - CRES, PASSIVATE.
2. MOUNTING HARDWARE SUPPLIED IN SEPERATE BAG WITHIN UNIT PACKAGE.
3. RECOMENDED HOLE DIAMETER FOR SOLDER PINS AS FOLLOWS:
- FOR .050 DIA PIN: .057-.067 DIA (2 PLCS).
 - FOR .080 DIA PIN: .095-.105 DIA (3 PLCS).
4. RECOMMENDED HOLE DIAMETER FOR MOUNTING STUDS: .150-.160 DIA (2 PLCS).

HARDWARE PACKAGE - P/N 450006700			
ITEM	PART NUMBER	DESCRIPTION	QTY
3	200001601	STUD	2
2	200008750	WASHER	2
1	200008800	SELF-LOCK NUT	2

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd		RELAY SOCKET 1 POLE BOARD MOUNT		
ANSI Y14.5M UNITS: INCHES Pro/E FILE	.XX ±0.01 .XXX ±0.005 ANGLES ±0.5°		ENGR B. LAWSON Dec-22-14				
ORIGINAL NOT FOR CUSTOMER DISTRIBUTION	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA		CHKD <i>[Signature]</i> 1/5/15	APP'D <i>[Signature]</i> 1/5/15	SIZE B	DWG NO. RSN112040	REV -
			CODE: 58982	SCALE: 1.000	SHEET 1 OF 1		