




ITEM #	PART #	QTY	DESCRIPTION	MATERIAL
1	SEE TABLE #1	1	SHELL ASS'Y	GLASS FILLED NYLON & 303 SS
2	AP-145-6	1	INSERT ASS'Y	DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS
3	AP-105-5	1	STRAIN RELIEF	NYLON
4	AP-105-6	1	FERRULE	STAINLESS STEEL
5	AP-105-8	1	NUT CLAMP	NYLON, BLACK PER MIL-P-17091

C AP-165-CP

TABLE #1

AUDIO PLUG #	MILITARY PART #	SHELL ASS'Y	Ø CABLE
AP-165/7-1	M55116/7-1	AP-165-1	Ø .165± .010
AP-165/7-2	M55116/7-2	AP-165-2	Ø .228± .010
AP-165/7-3	M55116/7-3	AP-165-3	Ø .250± .010
AP-165/7-4	M55116/7-4	AP-165-4	Ø .290± .010
AP-165/7-5	M55116/7-5	AP-165-5	Ø .320± .010



SECTION Z-Z

NOTES:
1) UNLESS OTHERWISE SPECIFIED, CONNECTOR MEETS ALL
GENERAL REQUIREMENTS & SPECIFICATIONS OF MIL-C-55116

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

						DWN.BY	MNF	DATE	MATERIAL		
						CHECKED BY	L SMITH	DATE	FINISH		
						APPR.BY	L SMITH	DATE	WEIGHT	SCALE = 1.00 :1	NEXUS STAMFORD,CONN
C	DEL: 12° ; 36° ; ADD: 36° ; 48° REF; AP-165/7-2; AP-165/7-5	226	8/31 2015	HR				9/9/97	TITLE		
B	ADD P/N'S IN P/L	101	2/25 2011	HR		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES & OR (mm)			AUDIO PLUG		
A	REVISED & REDRAWN ON CAD	0259	2/24 1997	LS		TOLERANCES: DECIMAL: ±.XX(X.X) ±.XXX(X.XX) ±.XXXX(X.XXX) ±.0X(0.X) ±.00X(0.0X) ±.000X(0.0XX)					
LET.	REVISION	CN #	DATE	CHK		FRACTION: ±X/XX ± X/XX ANGLES: ±X ° ±X °			DO NOT SCALE DWG.	SHEET 1 OF 1	SIZE C DWG. NO. AP-165-CP

NEXUS
STAMFORD, CONN