

Industrial 2.5GBase-TX PulseJack™ Integrated SMD Connector

Rugged latch-up/Down design for industrial and outdoor use



Features and Benefits:

- ④ Latch-Up, Latch-Down plug orientation options
- ④ Side entry, small footprint to minimize board space
- ④ Meets IEEE 802.3 specification for 2.5Gigabit
- ④ Industrial operating temperature -40 to +85°C
- ④ High performance for EMI suppression

Electrical Specifications @ 25°C - Operating Temperature -40°C to +85°C

Part Number*	Connector Orientation	LED Configuration (L/R)	EMI Fingers Configuration	Inductance (min) 100kHz, 0.1mA - Media Side	Isolation (Pri:Sec)
JXD0-0101NL	Latch-Down	Green/ Green-Orange	Top Only	180uH	2250VDC / 60sec
JXD0-0104NL	Latch-Down	Green-Yellow /Green-Yelow	None	180uH	2250VDC / 60sec
JXD0-0104NL	Latch-Down	Green-Yellow /Green-Yelow	Top Only	180uH	2250VDC / 60sec
JXD1-0101NL	Latch-Up	Green/ Green-Orange	Top Only	180uH	2250VDC / 60sec
JXD1-0104NL	Latch-Up	Green-Yellow /Green-Yelow	None	180uH	2250VDC / 60sec
JXD0-0105NL	Latch-Up	Green-Yellow /Green-Yelow	Top Only	180uH	2250VDC / 60sec

* Component marking will not include the "T" as that denotes product i to be shipped in Tape and Reel - see page 4 for details

Electrical Specifications @ 25°C - Operating Temperature -40°C to +85°C

Part Number	Insertion Loss (Max)	Return Loss* (dB MIN) 100Ω (±15Ω)			Cross Talk (dB TYP)			Common Mode Rejection (dB TYP)	
	1-125 MHz	1-40 MHz	60-120 MHz*	120-250 MHz*	1 MHz	30-60 MHz	125 MHz	1-30 MHz	30-200 MHz
JXD6-0001NL	-1.2dB	-20dB	-12dB	-8dB	-40dB	-35dB	-30dB	-35dB	-30dB
JXD6-0002NL	-1.2dB	-20dB	-12dB	-8dB	-40dB	-35dB	-30dB	-35dB	-30dB
JXD6-0003NL	-1.2dB	-20dB	-12dB	-8dB	-40dB	-35dB	-30dB	-35dB	-30dB
JXD6-0001NL	-1.2dB	-20dB	-12dB	-8dB	-40dB	-35dB	-30dB	-35dB	-30dB
JXD6-0002NL	-1.2dB	-20dB	-12dB	-8dB	-40dB	-35dB	-30dB	-35dB	-30dB
JXD6-0003NL	-1.2dB	-20dB	-12dB	-8dB	-40dB	-35dB	-30dB	-35dB	-30dB

* Return Loss is calculated using $-20 + [15 \times \log_{10}(f/40\text{MHz})]$

Notes:

1. ROHS Compliant:
2. Plastic housing: thermoplastic material with flammability rating UL 94V-0 or better
3. Contacts plating: 30 micro-inch gold plating
4. Contacts base material: Phosphor bronze
5. Under plating: 30 micro-inch min nickel
6. Solder Tail Plating: 100 micro-inch (min), inches 100% tin, matte finish
7. Metal shield nickel plating on Copper Alloy
8. Jack cavity conforms to FCC part 68 subpart
9. PCB plating: HASL
10. Storage temperature: -40°C to +85°C
11. Compliance to J-STD:
 - A. J-STD-002: solderability at 245°C DIP and LOOK test
 - B. J-STD-020: level 1, no moisture sensitive
 - C. J-STD-075: R7, 260°C maximum through Wave Solder
12. Parts come in full Trays of 50pcs


Industrial 2.5GBase-TX PulseJack™ Integrated SMD Connector

Rugged latch-up/Down design for industrial and outdoor use




MECHANICALS


JXD0-010xNL




Dimensions:
Unless otherwise specified,
all tolerances are $\pm 0,25$



JXD1-010xNL



Dimensions:
Unless otherwise specified,
all tolerances are $\pm 0,25$




Industrial 2.5GBase-TX PulseJack™ Integrated SMD Connector

Rugged latch-up/Down design for industrial and outdoor use




SCHEMATICS

JXD0-0101/4/5/NL



LEDs for JXD0-0101NL



LED SPECIFICATION

STANDARD LED	WAVELENGTH	FORWARD V(MAX)	TYP
GREEN	565nm	2.4V	2.2V
ORANGE	605nm	2.5V	2.0V

*WITH A FORWARD CURRENT OF 20mA

LEDs for JXD0-0104/5NL




LED SPECIFICATION


STANDARD LED	WAVELENGTH	FORWARD V(MAX)	TYP
GREEN	565nm	2.4V	2.2V
YELLOW	590nm	2.5V	2.1V

*WITH A FORWARD CURRENT OF 20mA

JXD1-0101/4/5/NL



LEDs for JXD1-0101NL



LED SPECIFICATION

STANDARD LED	WAVELENGTH	FORWARD V(MAX)	TYP
GREEN	565nm	2.4V	2.2V
ORANGE	605nm	2.5V	2.0V

*WITH A FORWARD CURRENT OF 20mA

LEDs for JXD1-0104/5NL



LED SPECIFICATION

STANDARD LED	WAVELENGTH	FORWARD V(MAX)	TYP
GREEN	565nm	2.4V	2.2V
YELLOW	590nm	2.5V	2.1V


*WITH A FORWARD CURRENT OF 20mA

100Base-TX PulseJack™ Integrated SMD Connector


Rugged latch-up design for industrial and outdoor use

PCB LAYOUTS

JXD0-010xNL




KEEP-OUT AREA (COMPONENT SIDE SHOWN)




RECOMMENDED PWB LAYOUT
(COMPONENT SIDE SHOWN)

JXD1-010xNL



KEEP-OUT AREA (COMPONENT SIDE SHOWN)



RECOMMENDED PWB LAYOUT
(COMPONENT SIDE SHOWN)

For More Information:

Americas - prodinfo_network_americas@yageo.com | Europe - prodinfo_network_emea@yageo.com | Asia - prodinfo_network_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2022. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.