




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF YAMAICHI ELECTRONICS DEUTSCHLAND GmbH. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF YAMAICHI ELECTRONICS DEUTSCHLAND GmbH IS PROHIBITED.



SPECIFICATION

Insulation Resistance: 1000M Ω at 500V DC
Withstanding Voltage: 500V AC for 1 Minute
Voltage Rating: 100V max.
Current Rating: 1A AC/DC max.
Contact Resistance: 40m Ω max. at 20mV max./10mA max.
Operating Temperature Range: -20°C ~ +90°C
Reflow Solder Temperature: 235°C max. for 3 sec.
Mating Cycles: 10,000


MATERIAL

Insulator: Glass Reinforced LCP UL94V-0
Push button: Glass Reinforced PBT UL94V-0
Cover: Stainless Steel
Contacts: Brass (C2680R-EH)
Mount ear: Brass (C2680R-H); Tin plated overall
CONTACT PLATING
Contact area: Gold flash plating over 40u" Nickel
Solder tail area: 100u" tin plating over 40u" Nickel

PART NUMBER:

CF050P-003-**-DS

contact plating, see spec.
Colour of Insulator
0: White
1: Black (only by request)
Ejector
0: Without
1: Right Side
90° SMT Contacts
Male
No. of Contacts
Series



Notes:

Tolerances ± 0.3 unless otherwise specified.

For PCB Layout, see drawing P(039)A01, sheet 1/2

Scale:	%	APP.	CHK.	DRW.	DSGN.
Dimension:	mm	11/09/99	11/09/99	10/09/99	10/09/99
Angle Proj.:	PA	WM	SAK	SAK	SAK



Deutschland GmbH

Classification: CF050P-003-**-DS

Title: Compact Flash I Adapter

90° SMT Type - Male, manual version

Sheet No.: 1 Rev.

Drawing No.: P(039)A01 2/2 D

Drawing I.D.: 752D-50M