





ISO VIEW



DETAIL A-A



NOTE:

1. MATERIAL: NORYL N190
2. FINISH: EXTERNAL SURFACE TO HAVE MOLD-TECH MT-11020 ETCH FINISH
SURFACE TO BE CLEAN AND FLASH FREE
3. DRAFT MUST BE WITHIN TOLERANCE
4. ALL RADII TO BE 0.2mm, U.O.S

Amphenol PCD Shenzhen
受控文件
2007年02月18日

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER				0	FIRST ISSUE	L.V	25-06-04	----
LINEAR	ANGULAR	CAD FILE: 52170032531110				REV.	CHANGE DETAILS	BY	DATE	CHG/No
X ± 0.5	X° ± 1°	DRN: LV				DATE: 25-06-04		TITLE: PLASTIC NUT		
X/K ± 0.1	X°/K° ± 30°	MNL: REFER TO NOTE 1				DATE: 21-10-04		7/16"-20UNF-2B		
X/KX ± 0.05	X°/K°X° ± 15°	FINISH: REFER TO NOTE 2				DATE: 21-10-04		(LARGE)		
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS		APP'D: P.M				DATE: 21-10-04		Amphenol		
DO NOT SCALE		SCALE: 2:1 UOS				PART No: 52170032-531		Drawing No. 52170032-531-1		
DIMENSIONS IN MILLIMETRES		THIRD ANGLE PROJECTION				SIZE: A4		SHEET 1 OF 1		