



1

2

3

RUBBER PART GENERAL TOLERANCE			
PART DIM.	1	②	3
0 TO 3	± 0.2	± 0.3	± 0.4
3 TO 6	± 0.2	± 0.4	± 0.5
6 TO 10	± 0.3	± 0.5	± 0.6
10 TO 18	± 0.3	± 0.6	± 0.8
18 TO 30	± 0.4	± 0.8	± 1.0
30 TO 50	± 0.5	± 1.0	± 1.5
50 TO 80	± 0.6	± 1.2	± 2.0
80 TO 120	± 0.7	± 1.4	± 2.5
120 TO 180	± 0.8	± 1.6	± 3.0
180 TO 250	± 1.0	± 2.0	± 4.0
250 TO 315	± 1.2	± 2.5	± 5.0
315 TO 400	± 1.5	± 3.0	± 6.0
400 TO 500	± 1.8	± 3.5	± 7.0
500 OVER	± 0.4 %	± 0.8 %	± 1.5 %



注記

1. 適用コネクタ品番: 7122-1884-40 ETC.
: 7223-1884-40 ETC.

NOTE

1. APPLICABLE PART NO. : 7122-1884-40 ETC.
: 7223-1884-40 ETC.

ISSUE MARK

				CUSTOMER		MATL. SILICONERUBBER		TREAT.	
				CUSTOMER PART NO.		CUSTOMER DWG NO.		SPEC. (BROWN) & FIN.	
90.07.25		N E W		C90-L871		M. K		NAME W TYPE CONNECTOR	
LET DATE		REVISION RECORD		NO.		CHKD		STD LIB NO.	
								RUBBER STOPPER	
								PART NO. 7157-3562-80	
								DWG NO. 7157-3562-80:R	
								TRIAL PART NO.	
								YAZAKI CORPORATION	

GENERAL TOLERANCE		VENDOR NO.				
10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
A ±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
C ±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15
SPECIFIED		WEIGHT				
RUBBER PART GENERAL TOLERANCE 2		9				

J. Endo	S. Yagi	K. Abe	SAKAI	S. IANBA
90.7.20	90.7.26	90.7.25	83.06.17	90.07.25

1

2

3