

FOR REFERENCE ONLY

SPECIFICATIONS:

AC RATING: 10 AMPS @115VAC (RESISTIVE LOAD)
5 AMPS @115VAC (INDUCTIVE LOAD)
3 AMPS @115VAC (LAMP LOAD)

DC RATING: 10 AMPS @28VDC (RESISTIVE LOAD)
5 AMPS @28VDC (INDUCTIVE LOAD)
3 AMPS @28VDC (LAMP LOAD)


MECHANICAL LIFE: 500,000 CYCLES
ACTION: MOMENTARY SNAP

OPERATING FORCE:
SERIES 20 & 30: 3 TO 5 POUNDS MOMENTARY
1/2 TO 2 POUNDS PUSH-PULL
SERIES 22 & 32: 2 TO 3 POUNDS MOMENTARY

WEIGHT: .050 POUNDS MAXIMUM
CASE: ALUMINUM ALLOY 2011-T3,
"EU" (ROHS COMPLIANT)
CLEAR ANODIZED IAW MIL-A-8625
GLASS FILLED NYLON

PLUNGER: DIALLYL PHTHALATE IAW MIL-M-14
BODY: THREADED #2-56 NC-2B

B NX202002B-XX





② | ①
CONTACT
ARRANGEMENT
(SPNC)

ORDERING INFORMATION:

NX202002B-00 SWITCH ONLY
NX202002B-60 SWITCH, MOUNTING HARDWARE
NX202002B-61 SWITCH, MOUNTING HARDWARE, TERNIMAL HARDWARE
NX202002B-00EU SWITCH (ROHS) ONLY
NX202002B-60EU SWITCH (ROHS), MOUNTING HARDWARE (ROHS)
NX202002B-61EU SWITCH (ROHS), MOUNTING HARDWARE (ROHS), TERNIMAL HARDWARE

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.



A	INITIAL RELEASE	5/23/08	EWT
LET.	REVISION	CN #	DATE

DWN. BY	EWT	DATE	5/23/08	MATERIAL	N/A
CHECKED BY		DATE		FINISH	N/A
APPR. BY		DATE		WEIGHT	—
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON				SCALE	N/A
				TITLE SWITCH SPNC MOMENTARY	
.XX .XXX ANGLES					
— ±.003 ±.5°		SIZE		DWG. NO.	
		B		NX202002B-XX	
DO NOT SCALE DWG.				SHEET 1 OF 1	