

COOPER Bussmann	TECHNICAL DATA	RATING AND TYPE	I ² t (AMPERE ² SECONDS)				NOM. WATTS LOSS
			PRE- ARCING	TOTAL AT 240V	TOTAL AT V	TOTAL AT V	
<u>RANGE</u> SEMICONDUCTOR <u>REF.</u> SF25H <u>CURRENT RATING</u> 40-200 AMPS <u>SPECIFICATION</u> <u>DRG. No.</u> E5785150 <u>DATE</u> MARCH 1990		SF25H40	50	600			7
		SF25H50	100	1,400			7
		SF25H60	170	2,200			9
		SF25H75	300	2,850			9
		SF25H100	670	6,700			11
		SF25H125	1,200	12,000			14
		SF25H140	1,800	18,000			15
		SF25H160	1,800	18,000			18
		SF25H200	2,800	26,000			21

