

[Photo](#) | [Dimensions](#) | [Mounting Hole Dimensions](#) | [Terminal Layout / Circuit Diagram](#) | [Packing Specifications](#) | [Soldering Conditions](#) |


PRINT

Part number		RS60N111900H
Number of resistor elements		Single-unit
Direction of lever		Vertical
Travel		60mm
Lever type		9-T (T-Bar)
Length of lever		8.2mm
Total resistance		10kΩ
Resistance taper		15A
Terminal style		For PC board
Operating temperature range		-10°C to +60°C
Electrical performance	Total resistance tolerance	±20%
	Maximum operating voltage	150V AC
	Rated power	0.1W
	Insulation resistance	100MΩ min. 250V DC
	Voltage proof	250V AC for 1 minute
Mechanical performance	Operating force	0.3(+0.5, -0.25)N
	Stopper strength	100N
	Lever push-pull strength	50N
	Lever wobble (Both side)	1.312mm
	Lever deviation (One side)	0.5mm max.
Durability	Operating life	30,000 cycles
Minimum order unit (pcs.)	Japan	300
	Export	600


Photo



Dimensions




Mounting Hole Dimensions



Viewed from mounting side.

Terminal Layout / Circuit Diagram



Packing Specifications

Tray

Number of packages (pcs.)	1 case / Japan	300
	1 case / export packing	600
Export package measurements (mm)		377×517×371

Soldering Conditions

Reference for Dip Soldering

Preheating	Soldering surface temperature	100℃ max.
	Heating time	1 min. max.
Dip soldering	Soldering temperature	260℃ max.
	Soldering time	5s max.
No. of solders		1 time

Reference for Hand Soldering

Tip temperature	350℃ max.
Soldering time	3s max.
No. of solders	1 time

Notes are common to this series/models.

1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
2. Please place purchase orders per minimum order unit (integer).
3. Products other than those listed in above products are also available. Please contact us for details.
4. "L" in the "Lever Wobble" column of the above table indicates the length of lever.

Inquiries about Products

 [Inquiry](#)