






THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Customer Drawing



Notices:

1. All non-dimensioned surfaces according to 3D-model &
2. Planeness of panel surface should less than or equal to 0.1mm
3. Roughness of panel surface should be $\sqrt{3}$ or better.
4. Thickness of panel should not exceed 12mm.



面板安装孔尺寸
Panel Size

规格参数 (Spec.):

1. 工作温度 Operating temperature:
-40° C ~ +125° C.
2. 带高压互锁 Electrical interlock (HVIL).
3. 额定电流 Current rating:
Power: 300A; HVIL: 5A.
4. 额定电压 Operating voltage:
Power: 1000 VDC; Signal: 60 VDC.
5. 耐电压 Dielectric withstanding voltage:
 - A. 与插头对插后, Pin与铁壳之间
After mating, between pin and metal shell :5000 VDC.
 - B. 与插头对插后, Pin与HVIL之间
After mating, between pin and HVIL :5000 VDC.
 - C. 与插头对插后, HVIL与铁壳之间
After mating, between HVIL and metal shell :500 VDC.
 - D. 与插头对插前, 两个HVIL端子之间耐压
Before mating, between two HVIL terminals :500 VDC.
6. 防护等级 Protection class: IP67 & IP2X.
7. 电磁屏蔽 Shielding.
8. 机械寿命 Mating cycle: 50 Min.
9. 带自动二次锁扣 Automatic secondary lock.
10. 铜排推荐安装扭矩 Recommended Fasten Torque on Lug:
M6 : 3.6~4.4 Nm
M8 : 7.2~8.8 Nm
M10: 17.1~20.9 Nm
11. 推荐法兰盘螺丝安装扭矩 Recommended Screw Assembly Torque on Flange : 6.2~7.6 Nm

订购信息 Ordering Information

PL082 X		- 30	1	- 20	M	8
键位及颜色 Key		高压互锁 HVIL		螺栓大小 Thread Size		
"X" Key		0, 不带互锁 No HVIL		M8		
"Y" Key		1, 带互锁 With HVIL				

REVISIONS					
REV	ZONE	ECO	DESCRIPTION	DATE	BY APPR
A	--	--	INITIAL RELEASE	05/21/14	RW EC
G	--	--	Add Dust Cap & Change HVIL Wire, Update Spec.	03/30/16	RW GX
H	--	--	Add Geometric Tolerance of Flange & Panel	10/21/16	RW PL
I	--	--	Change Shell and Gasket	05/09/17	Sam Julie

Standard Part List (With HVIL)

P/N	Model NO.	Mating Plug Model NO.
AC-HA001507	PL082X-301-20M8	PL182X-301-XX, PL282X-301-XX
AC-HA001508	PL082Y-301-20M8	PL182Y-301-XX, PL282Y-301-XX

Standard Part List (Without HVIL)

P/N	Model NO.	Mating Plug Model NO.
AC-HA000947	PL082X-300-20M8	PL182X-300-XX, PL282X-300-XX
AC-HA000948	PL082Y-300-20M8	PL182Y-300-XX, PL282Y-300-XX



Amphenol Technical Products International GZ

第三角投影 THIRD ANGLE PROJECTION		页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME: PwrLok 10mm 2POS Rcpt Conn	
		1 of 1	A3	I		DWG NO: PL082-300-20	
签名 SIGNATURE		日期 DATE	UNLESS OTHERWISE SPECIFIED			CUST PART #:	
制图 DRAWN		Sam	1) All dimensions are in metric (mm).			N/A	
审核 CHECKED		Julie	2) Tolerances are as follows:			CUST REV.	
批准 APPROVAL		Haley	0 PL DEC ±1.00 1 PL DEC ±0.50 2 PL DEC ±0.20			-	
			Angles ±1°				