




TABLE 1: LENGTH TOLERANCES

LENGTH (ft)	LENGTH (m)	TOLERANCE (ft)	TOLERANCE (m)
≤3.3	≤1.00	+ .33/-0	+0.10/-0
>3.3 TO ≤41.0	>1.00 TO ≤12.50	+ .83/-0	+0.25/-0
>41.0	>12.50	+2%/-0	+2%/-0



ADVANCED PRINT ONLY

FOR EVALUATION ONLY. CONTACT AMPHENOL ENGINEERING DEPT FOR THE CURRENT RELEASE AND SIGNED APPROVAL. PRIOR TO MANUFACTURING, THIS PRINT MAY BE UPDATED WITHOUT NOTICE.

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE		NOTE: These drawings, specifications, and data shall be the property of Amphenol Corporation. They shall be used only for the purpose for which they were prepared and shall not be used for any other purpose without the written consent of Amphenol Corporation. The user shall be responsible for obtaining all necessary permits and licenses for the use of this information. This may be subject to change without notice.		REV. A		FIRST ISSUE		DATE: 03/09/15	
LINEAR	ANGULAR	MATL:	FINISH:	DRN:	CKD:	DATE:	DATE:	TITLE: JUMPER, ST-ST, 3mm SIMPLEX, S/M	
XXX ±	XXX ±	XXX ±	---	---	---	---	---	Amphenol FIBER OPTIC PRODUCTS	
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS				APVD:		DATE:	DATE:	2100 GARDEN GL. SUITE 300, LOMA IL 60532, USA	
DO NOT SCALE				REF.:		DATE:	DATE:	942-31555-1YXXX	
DIMENSIONS IN MILLIMETERS				THIRD ANGLE PROJECTION		SCALE: NTS		PART No. SEE NOTE 2	
1				2		3		4	
5				6		7		8	

- NOTES:
- CABLE IS 3mm, S/M, SIMPLEX, YELLOW.
 - PART NUMBER 942-31555-1YXXX, WHERE:
Y=0 FOR MEASUREMENT UNIT IN METERS.
Y=F FOR MEASUREMENT UNIT IN FEET.
XXXX = LENGTH OF THE CABLE.
(i.e. 942-31555-10005=5 meters, 943-31255-1F005=5 feet)
 - COMPONENTS SHALL BE ROHS COMPLIANT AND MEET AMPHENOL REGULATED MATERIAL SPECIFICATIONS 949-1604.
 - DUST CAPS ARE NOT SHOWN FOR CLARITY.