




Technical specification:

Rated voltage: IEC 61076-2-104	50 V AC / 60 V DC
Current rating: IEC 61076-2-104	4 A at 40 °C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: EN 60512-11-10 EN 60512-11-4	-25 °C ... +95 °C -40 °C -40 °C ... +85 °C
Mating cycles: IEC 60512-9a	>=100

Materials:


Contact:	CuZn, Ni b / Au 0,2 gal.
Contact carrier:	LCP GF; UL 94 V-0
Shroud:	CuSn, nickel /sel. tin plated
Sealing:	FPM, NBR
Socket housing:	CuZn, Ni

Suitable for reflow soldering
max. 60s / 250 °C

Installation specification:

Recommended torque:	1-1,2 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220
Installation hole:	See fig.1 42K1A1119

Layout proposal




Part no. packing unit Tape & Reel:	Part no. packing unit in bulk:	Description:	Pos
42-01322TR	42-01322	SAL- 8S - FS4 - X13 / THR	4

DO NOT ALTER CAD DRAWING BY HAND

RoHS & REACH compliant

Index: a 08.04.16 KH Ä6018
Marking in mating face removed, contact carrier: material information extended



dim. in mm

	date	name
drawn	23.02.15	Gitinow
appd.	23.02.15	Schramm

general tolerance:	0 ± 0,50mm
	0,0 ± 0,25mm
	0,00 ± 0,10mm
	+ ± 5°

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

CONEC®

title:

Male socket M8x1 THR,
frontmounting,
screwable / snap-in

dwg no:

42K1A848

part no:

see table