


KIT PART NUMBER	CONNECTOR PART NUMBER	KIT TYPE	PCB PART NUMBER	CONTACTS QTY.	MS REF NUMBER
10-565997-322	91-565755-35P	II	10-407552-15	55	D38999/24FE35AN

REVISIONS			
LTR	DESCRIPTION	DATE	APPVD
A	INITIAL RELEASE NUM: <u>A2001-467</u>		

SEE NOTE 1



5. CONTACTS ARE NOT SUPPLIED FOR EXCESS CAVITIES.
4. PROCESS SPEC:
PROCESS SHEET CONTROL 9-4796
SPECIAL CONTROL 9-6000-2
3. PCB CONTACT STICKOUT LENGTH IS FROM REAR
OF CONNECTOR SHELL IF APPLICABLE.
2. PACKAGE PER PRODUCTION PROCESS SHEET.
1. KIT TYPE I CONTACTS SHIPPED UNASSEMBLED.
KIT TYPE II CONTACTS SHIPPED ASSEMBLED IN
CONNECTOR.

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

COMPANY ID: 9
INTERNAL: N
DATE CODE: N


CODING/MS/CUST: N
LOT NO: N
SEE DRAW: N

N/A
N/A
N/A

STAMPING DATA

NEXT ASSEMBLY

UNLESS OTHERWISE SPECIFIED	SPECIFICATIONS	POS	QTY	PART NUMBER	DESCRIPTION	NOTE
		PARTS LIST				
LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXXX = ±.0005 .XXX = ±.010 .XX = ±.03 .X = ±.1 ANGLES = ±2° OTHER STANDARDS PER 9-3800 AND DOD-D-1000 THIRD ANGLE PROJECTION	MATERIAL SPEC. N/A	APPROVALS		DATE	AMPHENOL CORPORATION BENDIX CONNECTOR OPERATIONS SIDNEY, N.Y. CONNECTOR KIT, TYPE MS TV-AB STAMPING JAM NUT	
		PREPARED	D. ALGER	11/29/01		
	CHECKED	<i>D. Jean</i>	11/29/01			
	MATERIAL	N/A PA	11/29/01			
	APPROVED	<i>A. Jean</i>	11/29/01			
	PROCESS SPEC. SEE NOTE 4	APPROVED	<i>E. Alger</i>	11/29/01		
	PROVING INFORMATION MODEL NAME DRAFT 10-565997-322		SIZE C	FSCM NO. 77820	DOCUMENT NO. 10-565997-322	REV. A
SCALE: NONE		REF: N/A	SHEET 1 OF 1			



E. Jean 11/30/01

10-565997-322

A