



Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



SPECIFICATIONS

Capacitance Value:	7,000 pF
Capacitance Tolerance:	+80, -20%
Temp. Characteristic:	X5W
Rating:	200 VDC @ + 85°C
Operating Range:	-55°C TO +85°C
Insulation Resistance:	10,000 megohms (min.) @ +25°C

NOTE:

1. MOUNTING TORQUE NOT TO EXCEED 5 lb-in.

REVISION RECORD Original Release C.O. 19990608-3-01 0		--TOLERANCES-- Unless Otherwise Specified	Title MINIATURE BUSHING FEED-THRU	
		DECIMAL ± .031		
		ANGLES ±	Drawn S.M. 06-09-99	Scale X 4
		TUSONIX TUCSON, ARIZONA	Approved E.F. 06-09-99	A 2425-000-X5W0-702Z