



Enter Your Keywords



SOLUTIONS PRODUCTS DESIGN SUPPORT BUY & SAMPLE ABOUT CYPRESS

Home > Products > CY8C4125AZA-M443T

CY8C4125AZA-M443T



Status: In Production

Product Specs	Pricing & Inventory	Packaging/Ordering	Quality and RoHS	Technical Documents
CY8C4125AZA-M443T				DESIGN SUPPORT
Automotive Qualified	Y			Development Kits
CPU Core	ARM Cortex-M0			Forums
CapSense	Y			Knowledge Base
Dedicated ADC (#Max Resolution @ Sample Rate)	SAR (1, 12-bit @ 806 ksp/s)			Packaging
EEPROM (KB)	0			Product Brochures
Flash (KB)	32			Quality & Reliability
JTAG and Si ID	0x1180			Samples
LCD Direct Drive	Y			Technical Support
Max. Operating Frequency (MHz)	24			Technical Training
Max. Operating Temp. (°C)	85			Third Party Network (CYPros)
Max. Operating Voltage (V)	5.50			
Min. Operating Temp. (°C)	-40			
Min. Operating Voltage (V)	1.71			
No. of CAN Controllers	0			
No. of Continuous Time Blocks	1			
No. of DMA Channels	8			
No. of Dedicated Comparators	2			
No. of Dedicated Timer/Counter/PWM Blocks	8			
No. of GPIOs	38			
No. of Op Amps	2			
No. of SIO	0			
No. of Serial Communication Blocks	4			
No. of USB IO	0			
No. of Universal Analog Blocks	0			
No. of Universal Digital Blocks	0			
PLL	N			
SRAM (KB)	4			
Series	PSoC 4100M			
Tape & Reel	Y			
USB (Type)	None			

PRICING & INVENTORY AVAILABILITY					
1-9 unit Price*	10-24 unit Price*	25-99 unit Price*	100-249 unit Price*	250-999 unit Price*	1000+ unit Price*
Contact Sales					

Availability	Quantity	Ships In	Buy from Cypress	Buy from Distributors
Out of Stock	0	Please click here to check lead times	Contact Sales	Contact Sales

* Prices are shown in United States dollars and are for budgetary use only for volume of 1ku

PACKAGING/ORDERING	
Package	TQFP
No. of Pins	44
Package Dimensions	275 L x 1.4 H x 275 W (Mils)
Package Cross Section Drawing	Download
Package Carrier	REEL
Standard Pack Quantity	1500
Minimum Order Quantity (MOQ)	1500
Order Increment	1500
Estimated Lead Time (days)	91
HTS Code	8542.31.0001
ECCN	(A.3)
ECCN Suball	3A991

QUALITY AND ROHS	
Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260 (Cypress Reflow Profile)
RoHS Compliant	Y Print RoHS Certificate of Compliance
PB Free	Y
Lead/Ball Finish	Ni/Pd/Au
Marking	Cypress Marking Format

Device Qualification Reports
FIT/MTBF, ESD (HBM/CDM) and Latch-up data available in the Device Qualification Report.
QTP#162707: AUTOMOTIVE PSoC 4100M and PSoC 4200M DEVICE FAMILY S8PFHD-10P, FAB25 (AL BEOL INTERCONNECT).pdf <i>Last Update: Mar 06, 2019</i>

TECHNICAL DOCUMENTS
Application Notes (17)
AN84858 - PSoC®4 Programming Using an External Microcontroller (HSSP) Jan 19, 2020
AN93637 - PSoC® 4 Sensorless Field-Oriented Control (FOC) Dec 30, 2019
AN82156 - PSoC® 3, PSoC 4, and PSoC SLP - Designing PSoC Creator™ Components With UDB Datapaths Oct 02, 2019
AN82250 - PSoC Creator - Implementing Programmable Logic Designs with Verilog Sep 22, 2019
Show More ▼

SOLUTIONS

Automotive
Industrial
Consumer

PRODUCTS

Wireless
Microcontrollers (MCUs)
Memory
Universal Serial Bus (USB)
Power Management
Touch Sensing
Clocks & Buffers

DESIGN SUPPORT

Community
Videos
Quality & Reliability
Product Roadmaps

ABOUT US

Investors
Careers

CORPORATE HEADQUARTERS

Cypress Semiconductor Corp.
198 Champion Court
San Jose, CA 95134 USA
Tel: +1-408-943-2600

CUSTOMER SERVICE SUPPORT

+1-800-541-4736
Hours:
8:00AM - 5:00PM (local time)
Create a MyCase
Cypress Developer Community

INTERNATIONAL SUPPORT

+1-408-943-2600
United States +1-800-541-4736
Hours:
4:30AM - 1:30PM (pacific time)
7:30PM - 4:30AM (standard time)

OTHER REQUESTS

Contact Us
Report a Website Problem
Report a Security Vulnerability

[ABOUT US](#) [CAREERS](#) [INVESTORS](#) [LEGAL](#)

