



Part Number: MDVO LC DUPLEX MODULE

MDVO LC Duplex Fiber Module

Product Description

MDVO LC Duplex Fiber Module. Available in several colors and fiber types.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Secured applications over fiber optic

Physical Characteristics (Overall)

Height:	0.63 m
Width:	0.63
Depth:	1.14
Packaging:	10 units packaged in a plastic bag.
Weight:	0.013 lbs

Connectors

Materials

Description	Material	Type
Front Connection	Plastic - UL94V-0	LC-Duplex
Rear Connection	Plastic - UL94V-0	LC-Duplex

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	MDVO
Connector/Hardware Retention:	20 lbs

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-07-01
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Part Number

Related Parts:	Compatible MDVO Faceplate and Patch Panel
----------------	---

Variants

Item #	Color	UPC
--------	-------	-----

AX102210	Almond	611589004589
AX102214	Almond	611589004626
AX102212	Black	611589004602
AX102216	Black	611589004640
AX102209	Gray	611589004572
AX102213	Gray	611589004619
AX102211	White	611589004596
AX102215	White	611589004633

Product Notes

Included Parts:	Dust Caps
Notes:	For additional information about this product, visit our web site at <a href="http://www.belden.com">http://www.belden.com</a> .

History

Update and Revision:	Revision Number: 0.166 Revision Date: 07-11-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.