




DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISIONS			2000-0005		SH 1
REV	EO	DESCRIPTION	DWN	APPROVED	DATE
B	5903	REV & REDWN	JEB	<i>JEB</i>	7-18-83
C	6248	REV P/L, ITEM 2 WAS 8000-0594	CMF	<i>CMF</i>	3-13-84



**RECOMMENDED
PANEL CUTOUT**
SCALE: NONE

INCH	MM
.160	4.06
.218	5.54
.221	5.61
.380	9.65
.505	12.83
.510	12.95
.525	13.34
.783	19.17
.794	20.17
1.308	33.22

△ CONTACTS, INSULATOR & "D" FLAT SHALL BE ORIENTED WITHIN $\pm 3^\circ$ OF ORIENTATION SHOWN

3. MAX PANEL THK .160
2. FINISH: TFS-1A (NICKEL)
1. ALL DIM ARE REF IN INCHES

THIN $\pm 3^{\circ}$

QTY	DESCRIPTION			PART NUMBER		ITEM
TOL UNLESS SPECIFIED .XX $\pm$.XXX $\pm$.XXXX $\pm$ ANGLES $\pm$			TROMPETER ELECTRONICS, INC.		BJ38	
DWN	JEB	6-16-83	MATERIAL	CODE IDENT	DRAWING NO.	REV
CHK	JEB	6-27-83	—	14949	2000-0005	C
ENGR	TW	7-14-83				
NEXT ASSY	APPR	3-13-84	SCALE 2/1	DATE 12-21-65	SHEET 1 OF 2	