







SYMBOL DEFINITION	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED
	16
	LAST NO. USED
	13

MISSING SYMBOLS
NO MISSING SYMBOL NUMBER

DWG STATUS				ZONE		REVISION HISTORY				AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P	CHG									
02JN06	R	C6	-	-			PD CREATED			281218	EES	EES	ET



43.3 MIN ALLOWABLE DUE TO BOW





NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA. ALL RADII 0.4
DRAFT IS 1° MAX ON ALL OUTSIDE SURFACES. LIKE CAVITIES ARE IDENTICAL.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CAVITIES TO ACCEPT 12047680 TERMINAL OR EQUIVALENT.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 12040926
RETAINER 15492535
BOLT 15492534
CABLE SEAL 12040936 (2 REQ'D)
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- CONNECTOR CAVITIES TO ACCEPT MAX. CABLE O.D. OF 2.4 MM.
- (2)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".
- MATERIAL RECYCLING CODE PER ISO 11469. (2)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO RECYCLING CODE.

(N/A)	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

DIMENSIONAL RANGE (MM)										CHART ET	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300		
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
±0.15										±1	±1.2
±0.2										±0.6	±0.8
±0.3										±1	±1.2
±0.4										±1	±1.2
±0.5										±1	±1.2
±0.6										±1	±1.2
±0.8										±1	±1.2
ANGULAR TOLERANCE										±2°	

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)		DISTR CODE	
10.873		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE DATED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
		USE MATH DATA	
			

DELPHI							
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH							
DR						DATE	
APVD1 E. SEIDEL						02JN06	
APVD2 E. SEIDEL						02JN06	
APVD3 E. TRACEY						05JN06	
APVD4							
APVD5							
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001							
MATERIAL M4698001 PBT GF 30 NAT							
DRAWING NAME							
CONN 18 F M/P 150 NAT SLD							
DRAWING NUMBER							
12040924							
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P	
A1	2:1	1 OF 1	1 OF 1	R	C6	-	