





SYMBOL DEFINITION			MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING	TOTAL NO. OF SYMBOLS ON DRAWING	50	59,67-71,	
	LAST NO. USED	104		




DWG STATUS				ZONE		REVISION HISTORY		AUTH	DR	CK	APVD
DATE	STG	REV	CHG	N/P							
16JUL01	R	B2	-	-			2.7 +0.2/-0.15 WAS 2.7, 23.5 +1.8/-0.3 WAS 23.5 +0.2/-0.3 & 4X 23.65 +0.15/-0.3 WAS 9X 23.65 TYP	211980	HH	EOV	JH
14SEP01	R	B3	-	-			ADDED OPTIONAL CONSTRUCTION NOTES & REVISED MATERIAL SPEC	214586	EOV	EOV	JH



SEE DETAIL "Y"

○ RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO

○ RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - SEALING CODE 0 - UNSEALED
 - MATING COMPONENTS OR EQUIVALENT: COVER 12110313

DELPHI Automotive Systems	
MATERIAL SPEC M3592001 PA66 HS 1M-BLK	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001	
PART DRAWING	
CODE NUMBER 6901	DWG DATE 06SE91
OC SPEC	SCALE 2:1
	VOLUME cm³ 13.278
PART GEOMETRY 3D SOLID	
UNLESS OTHERWISE SPECIFIED: THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M - 1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY. REGARDLESS OF DATUM REFERENCES.	
CHANGE RESTRICTED NO MANUAL CHANGES	REFERENCE
	DR
	DATE
COPY OF MATH DATA DO NOT SCALE	APVD1 GERALD CHAPMAN 06SE91
	APVD2 GERALD CHAPMAN 06SE91
	APVD3 R.A. PETROSKY 10SE91
	APVD4
	APVD5
METRIC UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS	DRAWING NAME BRACKET MT
THIRD ANGLE PROJECTION	

DIMENSIONAL RANGE (MM)				CHART E1			
FROM	TO	0	> 20	> 30	> 70	> 100	> 150
		20	30	70	100	150	200
		100	150	200	250	300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED				TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.15				±0.15			
±0.2				±0.2			
±0.3				±0.3			
±0.4				±0.4			
±0.5				±0.5			
±0.6				±0.6			
±0.8				±0.8			
±1.0				±1.0			
±1.2				±1.2			

(29) PROCESS SENSITIVE DIMENSION


DIMENSIONS ENCLOSED IN  INDICATE REWORKING DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

CHART E1

FROM TO 0 > 20 > 30 > 70 > 100 > 150 > 200 > 250 > 300 > 400

TOLERANCE UNLESS OTHERWISE SPECIFIED

±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1.0 ±1.2

ANGULAR TOLERANCE ± 2°

SHARP CORNER TOLERANCE

R 0.1 MAX

R 0.2 MAX

SHEET NUMBER				DRAWING NUMBER				DWG STATUS				SIZE
1	OF	1		12129359				STG	REV	N/P		A0
								R	B3	-		