


SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	6	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	6		

DWG STATUS				REVISION HISTORY		AUTH	DR	AP/VD
DATE	STG	REV	N/P	CHG	ZONE			
09MA07	R	01	-	-		RELEASED	285783	WDZ JWG WJG WJG
04JN08	R	01	AA	-		REMOVE NOT3	404947	WDZ JWG WJG WJG
10JL08	R	01	AB	-		REMOVE NOTE 2	405384	RZ JWG RZ
280C08	R	02	-	-		ADDED MARK AND NOTE.	406621	WGJ RZ JWG



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MATING PANEL HOLE $\varnothing 6.5 \pm 0.2$

DIMENSIONAL RANGE (MM)									
FROM	> 0	> 6	> 30	> 70	> 100	> 150	> 200	> 250	> 300
TO	6	30	70	100	150	200	250	300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED									
	±0.1	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2
ANGULAR TOLERANCE 22°									

(6) PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

DWG TYPE	
PART DRAWING	
STYLE	
VOLUME 10/1	DISTR CODE
1.82	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ISO 11454-1:1994 AS ISSUED BY THE ISO STANDARDS COMMITTEE. DIMENSIONS ARE TO FACE UNLESS OTHERWISE SPECIFIED. SEPARATE DIMENSIONS OF FEATURES MAY BE BASED SEPARATELY PER ISO 11454-1:1994 REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	NX

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WILSON, OH	
DR	DATE
AP/VD1 WEIDONG ZHANG	09MA07
AP/VD2 JIANWEI GUO	09MA07
AP/VD3 WEIDONG ZHANG	09MA07
AP/VD4	
AP/VD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
DRAWING NAME	
MOUN CLIP	
DRAWING NUMBER	
13603962	
SIZE A0	SCALE 2:1
FRAME NO 1	SHEET NO 1 OF 1
STG REV N/P	R 02 -