






1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PART USED IN ASSEMBLY 1360B209.
3. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CONNECTOR 1360B211

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CUP) 1.841		DISTR CODE D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS INTERPRETED BY THE DIM LINGUAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNING OF FEATURES MAY BE GIVEN SEPARATELY REGARDLESS OF DIMENSION REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
1	THIRD ANGLE PROJECTION	DO NOT SCALE	 
0		USE MATH DATA	
2			

DELPHI DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH									
DR								DATE	
APV01		KUN WU				170C06			
APV02		JIANWEI GUO				170C06			
APV03		KUN WU				170C06			
APV04									
APV05									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001									
MATERIAL M46G9001 PBT NAT									
DRAWING NAME									
LOCK SECONDARY TPA NAT									
DRAWING NUMBER									
13608216									
SIZE	SCALE	FRAME		SHEET		STO	REV	REP	REV
A0	5:1	1 OF 1		1 OF 1			01		-

5	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

DIMENSIONAL RANGE (MM)		CHART	P
FROM	TO	> 0 > 30 > 70 100	> 100 > 150 > 200 > 250 > 300 > 400
TOLERANCE UNLESS OTHERWISE SPECIFIED		.250	.300
± .0, ± .03 ± .04 ± .05 ± .06 ± .08		± .1	± .12
ANGULAR TOLERANCE ± .1°			