






DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- | | | | |
|--|---|-----------------|---|
| DWG TYPE | | PART DRAWING | |
| STYLE | | | |
| VOLUME (QW)
2.664 | | DISTR CODE
D | |
| UNLESS OTHERWISE SPECIFIED | | | |
| THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994
REVISIONS BY THE 8th EDITION, DIMENSIONING AND
TOLERANCING ADDENDUM-2003. SEPARATE PATTERNING OF
FEATURES MUST BE SHOWN SEPARATELY REGARDLESS OF DATUM
REFERENCES. | | | |
| ALL DIMENSIONS ARE IN MILLIMETERS | | | |
| REFERENCE | | | |
| 1 | THIRD ANGLE
PROJECTION | | DO NOT
SCALE |
| 2 | USE MATH DATA | |   |
| 3 |   | | |

7	PROCESS SENSITIVE DIMENSIONS																					
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED																						
DIMENSIONAL RANGE (MM) FROM TO	<table style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 16.6%; border-bottom: 1px solid black;">> 0</td> <td style="width: 16.6%; border-bottom: 1px solid black;">> 30</td> <td style="width: 16.6%; border-bottom: 1px solid black;">> 100</td> <td style="width: 16.6%; border-bottom: 1px solid black;">> 150</td> <td style="width: 16.6%; border-bottom: 1px solid black;">> 200</td> <td style="width: 16.6%; border-bottom: 1px solid black;">> 250</td> <td style="width: 16.6%; border-bottom: 1px solid black;">> 300</td> </tr> <tr> <td style="border-bottom: 1px solid black;">0</td> <td style="border-bottom: 1px solid black;">30</td> <td style="border-bottom: 1px solid black;">100</td> <td style="border-bottom: 1px solid black;">150</td> <td style="border-bottom: 1px solid black;">200</td> <td style="border-bottom: 1px solid black;">250</td> <td style="border-bottom: 1px solid black;">300</td> </tr> </table> TOLERANCE UNLESS OTHERWISE SPECIFIED <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 16.6%; border-bottom: 1px solid black;">±0.1</td> <td style="width: 16.6%; border-bottom: 1px solid black;">±0.3</td> <td style="width: 16.6%; border-bottom: 1px solid black;">±0.4</td> <td style="width: 16.6%; border-bottom: 1px solid black;">±0.5</td> <td style="width: 16.6%; border-bottom: 1px solid black;">±0.6</td> <td style="width: 16.6%; border-bottom: 1px solid black;">±0.8</td> <td style="width: 16.6%; border-bottom: 1px solid black;">±1</td> </tr> </table> ANGULAR TOLERANCE ±1°	> 0	> 30	> 100	> 150	> 200	> 250	> 300	0	30	100	150	200	250	300	±0.1	±0.3	±0.4	±0.5	±0.6	±0.8	±1
> 0	> 30	> 100	> 150	> 200	> 250	> 300																
0	30	100	150	200	250	300																
±0.1	±0.3	±0.4	±0.5	±0.6	±0.8	±1																