





SYMBOL DEFINITION			MISSING NUMBERS		DWG STATUS					ZONE	REVISION HISTORY				AUTH	DR	APVD 1	APVD 2
					DATE	STG	REV	N/P	CHG									
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	32			010C99	R	001	-	-	PART RELEASED; WAS PE076381				990005	DS	DS	DM	
					150C99	R	002	-	-	MATERIAL WAS PM002191-018 PBT-GRA DK				197438	TMN	TMN	DM	
					02AU01	R	002	AA	-	REVISED NOTE				212657	LMB	LMB	DS	
	LAST NO. USED	38			11MY05	R	02	AB	-	MAT'L SPEC WAS R0100108 AND ADDED RECYCLING CODE & DELPHI BRAND NOTES				266899	MM	MM	ET	



SEALING SURFACE #1 MUST BE FREE OF SURFACE DEFECTS FOR A DISTANCE OF 7.2mm FROM THIS SURFACE.




SEALING SURFACE #1



3X SEALING SURFACE #2 MUST BE FREE OF SURFACE DEFECTS FOR A DISTANCE OF 9.0mm FROM THIS SURFACE.

3X SEALING SURFACE #2



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:

TERMINAL 15305350 (1.25 AVSS)
PRIMARY LOCK REINFORCEMENT (PLR) 15326555
CONNECTOR SEAL 12047908
CABLE SEAL 15305351 (1.25 AVSS)
TERMINAL POSITION ASSURANCE LOCK (TPA) 15373418



3. CONNECTOR ENGAGE FORCE CODE 1.

4. FOR MATING CONFIGURATION REQUIREMENTS SEE 12162266.

5. MATERIAL RECYCLING CODE PER ISO 11469. (1.15)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.

6. (1.63)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".

DIMENSIONAL RANGE (MM)		CHART	E
FROM	TO		
0	20	20	30
20	30	30	70
30	70	70	100
70	100	100	100
100	100	100	100
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.15		±0.2	±0.3
±0.3		±0.4	±0.5
ANGULAR TOLERANCE		±2°	

DWG TYPE		PART DRAWING	
STYLE			
ISUZU			
VOLUME (CM³)		DISTR CODE	
1.770		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
001, 701			
THIRD ANGLE PROJECTION		DO NOT SCALE	
			
USE MATH DATA		UNIGRAPHICS	

DELPHI						
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH						
DR			DATE			
APVD1	D. SMUTNY		010C99			
APVD2	D. SMUTNY		010C99			
APVD3	D. MCNALLY		040C99			
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
MATERIAL M4695002 PBT-BLK						
DRAWING NAME						
CONN 3 F GT 150 BLK SLD						
DRAWING NUMBER						
15373425						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	02	AB