


SYMBOL DEFINITION			MISSING NUMBERS
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	7	
	LAST NO. USED	12	

DWG STATUS				REVISION HISTORY				AUTH	DR	CK	APVD
DATE	STG	REV	CHG	N/P	ZONE						
08SE00	R	001	-	-		RELEASED		000005	DJM	DJM	PP
100C00	R	001	-	AA		REVISED TOLERANCE		203895	JJC	JJC	PP
06FE01	R	001	-	AB		REVISED TOLERANCE		206714	JAK	JAK	PP



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE 'PA66-GF14' PER SAE J1344 TO APPEAR ON PART.
- MATING COMPONENTS OR EQUIVALENT:
CORE - 15401345
UPPER HOUSING - 15328944
- MAXIMUM HEIGHT DIFFERENCES BETWEEN TOP SURFACES OF THE CORE AND COVER WINGS WHEN ASSEMBLED IS 1 MM.
- TOOL CAVITY IDENTIFICATION SHOULD BE LOCATED NEAR GATE.

DELPHI Automotive Systems	
MATERIAL SPEC R0100211 PA66GF14HS 1M GRA MD	
DIMENSIONAL RANGE (MM) CHART E FROM 0 TO 20 20 TO 30 30 TO 70 70 TO 100 TOLERANCE UNLESS OTHERWISE SPECIFIED 10.15 ±0.21 ±0.31 ±0.41 ±0.5 ANGULAR TOLERANCE ±2°	
PART DRAWING	
CODE NUMBER 6900	DWG DATE 08SE00
OC SPEC	STYLE
SCALE 2:1	
VOLUME cm³ 11.001	
DISTR CODE D	
PART GEOMETRY 3D SOLID	
UNLESS OTHERWISE SPECIFIED: THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M - 1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
UG CHANGE RESTRICTED NO MANUAL CHANGES	
COPY OF MATH DATA DO NOT SCALE	
REFERENCE 001,701 15357201	DR D. MIZNER APVD1 D. MIZNER APVD2 D. MIZNER APVD3 P. POLITSKY APVD4 APVD5
DATE 08SE00 08SE00 08SE00 11SE00	
METRIC UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS	
THIRD ANGLE PROJECTION	
DRAWING NAME CONN 40W GT 150 (COVER)	

PROCESS SENSITIVE DIMENSION		
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		

SHEET NUMBER	DRAWING NUMBER	DWG STATUS	SIZE
1 OF 1	15401346	R 001 AB	A0