



SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	8	NO MISSING SYMBOL NUMBER	
			LAST NO. USED	
		8		



CWS STATUS				REVISION HISTORY				AUTH		DR		APVD	
DATE	STG	REV	N/P	CHG	ZONE								
11JUL01	R	01	-	-		ALL ACTIVE PARTS - REVISED GRAPHICS		211315	RVP	RVP	JH		
17JUL03	R	02	-	-		12020156 - PER ECN 211315 REV LEVEL L2 SHOULD BE K1, CORRECT REV LEVEL TO K2		243603	JYD	JYD	JH		
01AUG06	R	03	-	-		12020156, 12033997 & 12066614 - MAT'L SPEC WAS P1519030		283052	MDH	JAA	MM		
18FEB15	R	04	-	-		12176854 - ADDED TARNISH INFO NOTE		428877	ABH	JVM	JSM		



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- RECOMMENDED MATING BLADES - (1) METRI-PACK (0.86/0.79 THK. X 6.38/6.22 WIDE)
(2) AUTOFUSE (0.69/0.61 THK X 5.355/5.11 WIDE)
- THIS PART FOR DIAGNOSTIC INDUSTRY APPLICATIONS.
- DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
- FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER, TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE PERFORMANCE OF THE PART.

PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PLATED	CABLE	TYPE	±0.4
12066506	A	-	0.406 X 35.71	COPPER ALLOY	12020156	K3	-	0.406 X 35.71	AG PLATED COPPER ALLOY	5 - 3	11	4.48-2.74	102 14.6
12066505	B	-	0.406 X 35.71	COPPER ALLOY	12066614	A2	-	0.406 X 35.71	TIN PLATED COPPER ALLOY	0.8 - 0.5	19	3.13-1.87	103 3.2
12066504	B	-	0.406 X 35.71	COPPER ALLOY	12033997	E3	-	0.406 X 35.71	TIN PLATED COPPER ALLOY	2 - 1	15	3.97-3.14	102 3.7
					12020157	H	-	0.406 X 35.71	TIN PLATED COPPER ALLOY	2 - 1	15	3.97-3.14	101 3.7
UNPLATED					PLATED								
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PLATED	CABLE	TYPE	±0.4

PROCESS SENSITIVE DIMENSION			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	CHART C2		
FROM 0 TO 12	> 12		
TOLERANCE UNLESS OTHERWISE SPECIFIED	±0.1	±0.2	±0.3
ANGULAR TOLERANCE ±2°			

THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA	USE MATH DATA	USE MATH DATA	USE MATH DATA

DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH COPYRIGHT 1988 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DATE	
DR	
APV01 J. KRAUSE	15MR88
APV02 D. STEELE	14AP88
APV03 G. SMALDINO	21AP88
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT, PER DELPHI (9244990)	
MATERIAL SEE CHRT	
DRAWING NUMBER	
TAXI TERM F W/P 630	
12020155	
SIZE A0	SCALE 8:1
FRAME NO 1 OF 1	SHEET NO 1 OF 3
STG REV R 04	N/P