






Notes:

- Electrical Specifications:
 - Meets EIA/TIA-568-B.2 Cat.5e Specification
 - Contact Resistance: 20mOhm max.
 - Insulation Resistance: 500MOhm min. @ 100 VDC
 - Current Rating: 1.2A max. at 25° C
 - Working Voltage: 100 VDC
 - DWV: 1000 VDC/60s Contact to Contact, 1500 VDC/60s Contact to Metal Shell
 - Operating Temperature: -40° C to +85° C
- Material and Finish:
 - Receptacle Housing, Metal Cover, Panel Nut: Brass, Nickel Plated
 - Ball Chain: Copper Alloy, Nickel Plated
 - Panel Gasket: Silicone, Color: White
 - Cover Gasket: Silicone, Color: Red
 - RJ45 PCB Jack Metal Shell: Copper Alloy, Nickel Plated
 - RJ45 PCB Jack Plastic Housing: Glass filled PBT UL94 V-0, Color: Black
 - RJ45 PCB Jack Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
- Connector can be front or rear mounted to a maximum panel thickness of 3.2mm.
- RoHS compliant

Directive 2002/95/EC
"RoHS"
Compliant

Description	Part Number
Metal Version Receptacle + Cover with Shielded RJ45 PCB Jack	17-101654
Potted Metal Version Receptacle + Cover with Shielded RJ45 PCB Jack	17-101674

Customer:			Tolerance Unless otherwise specified			Scale: 1:2:1	Dim. in mm
Name	Title	Approval Date	0 PLC	±0.50			
			1 PLC	±0.38	Autodesk Inventor	Material: See Notes	Title: Receptacle + Cover Assembly Kit with Cat. 5e RJ45 PCB Jack Metal Version
			2 PLC	±0.25			
			3 PLC	±0.10			
			ANGLES	±3°	Norm	Drawing No.: 17K1A252	DIN A3
b	Aug/26/09	Vincent ke	D-old			Part No.: SEE P/N TABLE	Sheet 1/1
a	original						
Rev.	Changes	Date	Name				