








TYPE 102

SAME AS TYPE 101
EXCEPT AS SHOWN






TYPE 103

SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 104



SAME AS TYPE 101
EXCEPT AS SHOWN



STAMP DIE ID "PXX" IN THIS AREA (0.61
CHARACTERS XX DESIGNATES DIE NUMBER



TYPE 101



CARRIER STRIP VIEW

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)
FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR
TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. TERMINAL ENGAGE BN TO ION TERMINAL. DISENGAGE 1.5N TO BN
WHEN MATED TO A 0.81 THICK X 1.5 WIDE HARDENED STEEL BLADE.
3. "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE SERIES
NUMBER (P01, P02, P03, ETC.).
4. DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE
SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN
OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
5. MATERIAL USED IS C654 - TIN PLATED SILICON BRONZE

		0.25 X 29	13964643	01	AA	RESTRICTED	SEE NOTE #5	1-0.8	17	2.4-1.7	101	4.2	2.8	10.08	3	2.6
		0.25 X 29	13964351	01	AA	RESTRICTED	SEE NOTE #5	0.5-0.35	21	2.2-1.3	101	3.5	2.1	10.08	-	2.1
		0.25 X 29	13737252	01	AB	-	COPPER ALLOY TIN PLATED	0.22-0.13	25	1.1-0.81	104	1.9±0.2	1.6±0.1.5	10.08	1.9	1.45
		0.25 X 29	15317766	03	AF	-	COPPER ALLOY TIN PLATED	0.5-0.35	21	1.3-1.2	101	2.3	2.1	10.08	-	-
		0.25 X 29	15305306	03	AF	-	COPPER ALLOY TIN PLATED	0.35-0.6	226	-	104	4.2	2.8	10.08	-	-
		0.25 X 29	12150812	03	AF	-	COPPER ALLOY SELECTIVE GOLD PLATED	1-0.8-0.5	17	2.4-1.7	101	4.2	2.8	10.08	-	-
		0.25 X 29	12124730	B	-	-	COPPER ALLOY TIN PLATED	1-0.8	17	2.4-1.7	101	4.2	2.8	10.08	-	-
		0.25 X 29	12064971	06	AH	-	COPPER ALLOY TIN PLATED	0.5-0.35	21	2.2-1.3	101	3.5	2.1	10.08	-	2.1
		0.25 X 29	12052466	07	AG	-	COPPER ALLOY TIN PLATED	0.2	24	1.2	104	2.6	1.5 ±0.1	10.08	-	-
		0.25 X 30.18	12049140	F1	-	-	COPPER ALLOY TIN PLATED	1	16	2.64-2.48	103	4.7	3.6	10.08	-	-
		0.25 X 29	12047767	11	AK	-	COPPER ALLOY TIN PLATED	1-0.8	17	2.4-1.7	101	4.2	2.8	10.08	3	2.6
		0.25 X 30.18	12047687	F1	-	-	COPPER ALLOY TIN PLATED	0.35	22	2-1.84	101	3.4	2.2	10.08	-	-
PART	NO	REV	N/P	MAT'L	SIZE	MAT'L SPEC	PART	NO	REV	N/P	RESTRICTED	MAT'L SPEC	SIZE (MM)	ID	DIA	TYPE
						UNPLATED										

DRAWING NUMBER
12047884

SIZE 10:1 SCALE FROM NO 12 OF 21 OF 7 R 20

DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE

DATE 20AUG96
BY FRANCISCO KOPKA
T. DUTILE
220036

12047884

10:1 1 OF 2 1 OF 7 R 20