



SYMBOL DEFINITION		MISSING NUMBERS	DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD1	APVD2
			DATE	STG	REV	N/P	CHG					
THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	4	15MY02	R	04	-	-	CLEARED REV COLUMN: ALL PARTS - REVISED NOTE 2	224776	EGR	EGR	00
	LAST NO. USED	4	07JN02	R	05	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	226564	TLD	TLD	PMJ
			05MY06	R	06	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	280180	RTV	JAA	CSD
			07AU12	R	07	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	419181	AH	AH	AH




CONDUCTOR WINGS FOR (SEE CHART) MM² CABLE

INSULATION WINGS FOR (SEE CHART) MAX INSULATION DIA.




- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 12160542
TERMINAL 12084912



VIEW SCALE DOES NOT REFLECT ACTUAL PART SIZE

12160552	02	AE		0.203 THK X T.B.D. CDA 425 1/2 HD TIN BRASS	PM003607	0.35-0.5	-	21	2.3	23.95
12160551	02	AE		0.203 THK X T.B.D. CDA 425 1/2 HD TIN BRASS	PM003607	0.5-0.8	2.04	18/20	2.8	23.95
PART NO	REV	N/P	STATUS	MAT'L SIZE & DESCRIPTION	SPECIFICATION	SIZE (MM ²)	DIA±0.08	I.D. NO.	D±0.2	(K)

(2) PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART D
FROM 0 TO 12	> 12
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE	±2°

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (CM ³)	DISTR CODE
	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
12110797	
THIRD ANGLE PROJECTION	DO NOT SCALE
	
USE MATH DATA	NX

DELPHI						
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE						
WARREN, OH						
COPYRIGHT 2000 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.						
REVISED 2012						
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.						
DR	DATE					
APVD1 A. ARZATE	15MY00					
APVD2 FCO. RESENDIZ	07JL00					
APVD3 G. ORANTES	08JL00					
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001						
MATERIAL SEE CHART						
DRAWING NAME						
TAXI TERM M MIC/P 100W						
DRAWING NUMBER						
12160550						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	10:1	1 OF 1	1 OF 1	R	07	-