


6 5 4 3 2 1 used for: D-SUB COMBINATION



NOTES:

1. METALSHELLS: STEEL; min. 315µ" TIN over 40-80µ" NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING MATING AREA: 30µ" HARD GOLD OVER min. 50µ" NICKEL
4. NO CONTACTS ON POS. A1 + A2
5. THREADED SPACER CLIP: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 2,3mm
6. COLLAR: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
7. P.C.B. HOLE DRILLINGS ON SHEET 2
8. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
9. CONNECTOR IS PART MARKED: 3027W2SCR99C40X CONEC ABC

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm
drawn	17.05.06 Schmidt
appd.	17.05.06 Mickenbecker
norm	
d-old	

CONEC

scale:	2:1 (5:1)
material:	SEE NOTES
title: D-SUB COMBINATION FEMALE 27W2S with threaded spacer clip	
dwg no:	AutoCAD 2004 DIN-A
13K1A1784	
part no: 3027W2SCR99C40X	

B

A