









Recommended Double-D Panel Cutout



Recommended Round Panel Cutout



Notes:

- Material and Finish:
 - Receptacle Housing + Protective Cover: Die-Cast, Nickel Plated
 - Cover Gasket: Silicon, Color: White
 - Sleeve: Aluminum
 - Wire: Stainless steel
 - Lug: Copper Alloy, Nickel Plated
- Connector can be front or rear mounted to a maximum panel thickness of 3.2mm.
- IP67 rated when covered or fully mated with the appropriate mating connector
- The panel gasket (P/N: 17-103540) and the M3 mounting hardware (P/N: 17-103530) must be ordered separately.
- the recommended mounting torque is 8 to 10 lb-inch

Directive 2002/95/EC RoHS Compliant

Description	Part Number
Single Mode (SM) + Cover Assembly	17-300980
Multi Mode (MM) + Cover Assembly	17-300990
APC Single Mode (APC SM) + Cover Assembly	17-301000

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. CONECSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:			Tolerance Unless otherwise specified			Scale:	Dim. in mm
	Name		Title	Approval Date				
							Autodesk Inventor	Material: See Notes
						Title: IP67 Industrial Duplex LC Receptacle (with Flange) + Cover Kit Nickel Plated Zinc Die-Cast Version		
							Drawing No.: 17K1A527	DIN A3
						Part No.: SEE PART NUMBER TABLE		