




NOTES:

1. METALSHELLS.STELL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
4. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. CONNECTOR WILL BE SUPPLIED WITHOUT CONTACTS
6. MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
7. CONNECTOR IS PART MARKED: DSS1XSXXG03X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance			 dim. in mm		scale:		2:1 (5:1)					
															material:		SEE NOTES					
															date	name		title: D-SUB FEMALE CRIMP STYLE 9pos. with threaded insert				
															drawn	27.06.12	Henneboel					
															appd.	27.06.12	Koch					
															norm							
															d-old							
																		dwg no:		DIN-A3 sh: 1		
										a	Original							16K1A3082				
										rev.	description	date	name							part no:		DSS1XSXXG03X

CONEC®