


D-Subminiature connectors




smaller version:
connector with metal bracket flush

•370 inch

Solder pin angled
with riveted metal bracket


Socket connector



Kat 1 i K0A

No. of pos.	A - 0.76	B - 0.25	C
9	31,19	16,46	25,00 ^{+0.12} / _{-0.13}
15	39,52	24,79	33,30 ^{+0.15} / _{-0.10}
25	53,42	38,50	47,04 ^{+0.13} / _{-0.10}
37	69,70	54,96	63,50 ^{+0.13} / _{-0.10}

Plug connector



Kat 1 i K1A ohne Schirmfeder

No. of pos.	A - 0.76	B + 0.25	C	D - 0.30
9	31,19	16,79	25,00 ^{+0.12} / _{-0.13}	6,12
15	39,52	25,12	33,30 ^{+0.15} / _{-0.10}	6,12
25	53,42	38,84	47,04 ^{+0.13} / _{-0.10}	5,99
37	69,70	55,30	63,50 ^{+0.13} / _{-0.10}	5,99


Part numbers

No. of Pos.	Socket connector – solder pin angled	
	yellow zinc	tin-plated
9	CDF 09 ABWMKN 162 A 12919 X	CDF 09 ABWMKNSN 164 A 13289 X
15	CDF 15 ABWMKN 162 A 12929 X	CDF 15 ABWMKNSN 164 A 13299 X
25	CDF 25 ABWMKN 162 A 12939 X	CDF 25 ABWMKNSN 164 A 13309 X
37	CDF 37 ABWMKN 162 A 12949 X	CDF 37 ABWMKNSN 164 A 13319 X

No. of Pos.	Plug connector – solder pin angled	
	yellow zinc without ground indent	tin-plated with ground indent
9	CDS 09 ABWMKN 161 A 14269 X	CDS 09 AFBWMKNSN 163 A 14809 X
15	CDS 15 ABWMKN 161 A 14279 X	CDS 15 AFBWMKNSN 163 A 14819 X
25	CDS 25 ABWMKN 161 A 14289 X	CDS 25 AFBWMKNSN 163 A 14829 X
37	CDS 37 ABWMKN 161 A 14299 X	CDS 37 AFBWMKNSN 163 A 14839 X



Part Number




Order example

Plug connector Solder bucket 25 pos. without printing			
Quality class		Part Number	
3		CDS 25 L	161 A 10039 X
2		CDS 25 L	161 B 10039 X
1		CDS 25 L	161 C 10039 X


D-Subminiature connectors

Hole pattern for straight and angled solder pins D-Sub standard


9 pos




37 pos




15 pos



25 pos



50 pos



Kat 1 i U3A

Kat 1 i U4A

Technical Data	D-Sub Standard	D-Sub High Density
Initial contact resistance	≤ 10 mΩ	≤ 10 mΩ
Initial insulation resistance	Quality class 1 ≥ 5GΩ Quality class 2 ≥ 5GΩ Quality class 3 ≥ 5GΩ	Quality class 1 ≥ 5GΩ Quality class 2 ≥ 5GΩ Quality class 3 ≥ 5GΩ
Clearance distance	contact–contact ≥ 1.0 mm contact–ground ≥ 1.2 mm	≥ 0.6 mm
Creepage distance	contact–contact ≥ 1.0 mm contact–ground ≥ 1.2 mm	≥ 0.6 mm
Test voltage V. r. m. s./NM	1000 V	1000 V
Working voltage/Insulation group* * nach SEV 50 V – acc. to SEV 50 V	125 V ≈	60 V ≈
Working current 20° C	5 A max.	25 A max.
Operating temperature	- 55° C – + 125° C	- 55° C – + 125° C
Moulding material	Polyester GF UL 94 V-O	PA 6.6 GF 25 UL 94 V-O
Contact material	Copper alloy	Copper alloy
Contact finish	hard-gold-plated over nickel	hard-gold-plated over nickel
Shell	Sheet steel, zinc lined and yellow chromate Sheet steel, nickel underneath and tin-plated	Sheet steel, nickel underneath and tin-plated
Insertion and withdrawal froces	9-polig/way 30 N 15-polig/way 50 N 25-polig/way 83 N 37-polig/way 123 N 50-polig/way 167 N	15-polig/way 50 N 26-polig/way 84 N 44-polig/way 120 N 62-polig/way 170 N 78-polig/way 200 N
Quality classes	Quality class 1 Quality class 2 Quality class 3	500 mating cycles 200 mating cycles 50 mating cycles