

Product Specs	Pricing & Inventory	Packaging/Ordering	Quality and RoHS	Technical Documents
CY8C4126AZA-M443				
Automotive Qualified	Y			
CPU Core	ARM Cortex-M0			
CapSense	Y			
Dedicated ADC (#Max Resolution @ Sample Rate)	SAR (1, 12-bit @ 806 kspS)			
EEPROM (KB)	0			
Flash (KB)	64			
JTAG and Si ID	0x1182			
LCD Direct Drive	Y			
Max. Operating Frequency (MHz)	24			
Max. Operating Temp. (°C)	85			
Max. Operating Voltage (V)	5.50			
Min. Operating Temp. (°C)	-40			
Min. Operating Voltage (V)	1.71			
No. of CAN Controllers	0			
No. of Continuous Time Blocks	1			
No. of DMA Channels	8			
No. of Dedicated Comparators	2			
No. of Dedicated Timer/Counter/PWM Blocks	8			
No. of GPIOs	38			
No. of Op Amps	2			
No. of SIO	0			
No. of Serial Communication Blocks	4			
No. of USB IO	0			
No. of Universal Analog Blocks	0			
No. of Universal Digital Blocks	0			
PLL	N			
SRAM (KB)	8			
Series	PSoC 4100M			
Tape & Reel	N			
USB (Type)	None			

PRICING & INVENTORY AVAILABILITY

1-9 unit Price*	10-24 unit Price*	25-99 unit Price*	100-249 unit Price*	250-999 unit Price*	1000+ unit Price*
Contact Sales					

Availability	Quantity	Ships In	Buy from Cypress	Buy from Distributors
Out of Stock	0	Please click here to check lead times	Contact Sales	Contact Sales

* Prices are shown in United States dollars and are for budgetary use only for volume of 1ku

PACKAGING/ORDERING

Package	TQFP
No. of Pins	44
Package Dimensions	275 L x 1.4 H x 275 W (Mils)
Package Cross Section Drawing	Download
Package Carrier	TRAY
Standard Pack Quantity	250
Minimum Order Quantity (MOQ)	250
Order Increment	250
Estimated Lead Time (days)	91
HTS Code	8542.31.0001
ECCN	(A3)
ECCN Suball	3A991.A.3

QUALITY AND ROHS

Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260 (Cypress Reflow Profile)
RoHS Compliant	Y Print RoHS Certificate of Compliance
Pb Free	Y
Lead/Ball Finish	Sn/Pb/Au
Marking	Cypress Marking Format

Device Qualification Reports

IFT/MTBF, ESD (HBM/CDM) and Latch-up data available in the Device Qualification Report.
 QTP#162707: AUTOMOTIVE PSOC 4100M and PSOC 4200M DEVICE FAMILY S8PFHD-10P, FAB25 (AL BEOL INTERCONNECT).pdf Last Update: Mar 06, 2019

TECHNICAL DOCUMENTS
Application Notes (17)

AN84858 - PSOC®4 Programming Using an External Microcontroller (HSSP) Jan 19, 2020
 AN93637 - PSOC® 4 Sensorless Field-Oriented Control (FOC) Dec 30, 2019
 AN82156 - PSOC® 3, PSOC® 4, and PSOC® 5LP - Designing PSOC Creator™ Components With UDB Datapaths Oct 02, 2019
 AN82250 - PSOC Creator - Implementing Programmable Logic Designs with Verilog Sep 22, 2019
 Show More ▾

SOLUTIONS

Automotive

Industrial

Consumer

PRODUCTS

Wireless

Microcontrollers (MCUs)

Memory

Universal Serial Bus (USB)

Power Management

Touch Sensing

Clocks & Buffers

DESIGN SUPPORT

Community

Videos

Quality & Reliability

Product Roadmaps

ABOUT US

Investors

Careers

CORPORATE HEADQUARTERS

 Cypress Semiconductor Corp.
 198 Champion Court
 San Jose, CA 95134 USA
 Tel: +1-408-943-2600

CUSTOMER SERVICE SUPPORT

 +1-800-541-4736
 Hours:
 8:00AM - 5:00PM (local time)
 Create a MyCase
 Cypress Developer Community

INTERNATIONAL SUPPORT

 +1-408-943-2600
 United States +1-800-541-4736
 Hours:
 4:30AM - 1:30PM (pacific time)
 7:30PM - 4:30AM (standard time)

OTHER REQUESTS

 Contact Us
 Report a Website Problem
 Report a Security Vulnerability