

CY8C4125AZA-M445T

Status: In Production



SOLUTIONS PRODUCTS DESIGN SUPPORT BUY & SAMPLE ABOUT CYPRESS

Product Specs

Pricing & Inventory

Packaging/Ordering

Quality and RoHS

Technical Documents

CY8C4125AZA-M445T

Automotive Qualified	Y
CPU Core	ARM Cortex-M0
CapSense	Y
Dedicated ADC (#Max Resolution @ Sample Rate)	SAR (1, 12-bit @ 806 ksp/s)
EEPROM (KB)	0
Flash (KB)	32
JTAG and SI ID	0x1181
LCD Direct Drive	Y
Max. Operating Frequency (MHz)	24
Max. Operating Temp. (°C)	85
Max. Operating Voltage (V)	5.50
Min. Operating Temp. (°C)	-40
Min. Operating Voltage (V)	1.71
No. of CAN Controllers	0
No. of Continuous Time Blocks	1
No. of DMA Channels	8
No. of Dedicated Comparators	2
No. of Dedicated Timer/Counter/PWM Blocks	8
No. of GPIOs	51
No. of Op Amps	2
No. of SIO	0
No. of Serial Communication Blocks	4
No. of USB IO	0
No. of Universal Analog Blocks	0
No. of Universal Digital Blocks	0
PLL	N
SRAM (KB)	4
Series	PSoC 4100M
Tape & Reel	Y
USB (Type)	None

DESIGN SUPPORT

Development Kits
Forums
Knowledge Base
Packaging
Product Brochures
Quality & Reliability
Samples
Technical Support
Technical Training
Third Party Network (CYPros)

TRAINING

Workshops
Training On-Demand
Webinars

PRICING & INVENTORY AVAILABILITY

1-9 unit Price*	10-24 unit Price*	25-99 unit Price*	100-249 unit Price*	250-999 unit Price*	1000+ unit Price*
Contact Sales					

Availability	Quantity	Ships In	Buy from Cypress	Buy from Distributors
Out of Stock	0	Please click here to check lead times	Contact Sales	Contact Sales

* Prices are shown in United States dollars and are for budgetary use only for volume of 1ku

PACKAGING/ORDERING

Package	TQFP
No. of Pins	44
Package Dimensions	393 L x 1.4 H x 393 W (Mils)
Package Weight	338.95 (mgs)
Package Cross Section Drawing	Download
Package Carrier	REEL
Standard Pack Quantity	1500
Minimum Order Quantity (MOQ)	1500
Order Increment	1500
Estimated Lead Time (days)	91
HTS Code	8542.31.0001
ECCN	(A.3)
ECCN Suball	3A991

QUALITY AND ROHS

Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260 (Cypress Reflow Profile)
RoHS Compliant	Y Print RoHS Certificate of Compliance
PB Free	Y
Lead/Ball Finish	Ni/Pd/Au
Marking	Cypress Marking Format

IPC 1752 Material Declaration

IPC 1752 MATERIAL DECLARATION TQFP64 (10X10 mm) (AZ64)_ASEK_Au WIRE_PURE Sn_HENKEL 8340_HITACHI CEL9200THF Last Update: Oct 30, 2019

Device Qualification Reports

FIT/MTBF, ESD (HBM/CDM) and Latch-up data available in the Device Qualification Report.

QTP#162707: AUTOMOTIVE PSoC 4100M and PSoC 4200M DEVICE FAMILY SBPFHD-10P, FAB25 (AL BEOL INTERCONNECT).pdf Last Update: Mar 06, 2019

TECHNICAL DOCUMENTS

Application Notes (17)

AN84858 - PSoC®4 Programming Using an External Microcontroller (H55P) Jan 19, 2020
AN93637 - PSoC® 4 Sensorless Field-Oriented Control (FOC) Dec 30, 2019
AN82156 - PSoC® 3, PSoC 4, and PSoC 5LP - Designing PSoC Creator™ Components With UDB Datapaths Oct 02, 2019
AN82250 - PSoC Creator - Implementing Programmable Logic Designs with Verilog Sep 22, 2019
[Show More](#)

SOLUTIONS

Automotive
Industrial
Consumer

PRODUCTS

Wireless
Microcontrollers (MCUs)
Memory
Universal Serial Bus (USB)
Power Management
Touch Sensing
Clocks & Buffers

DESIGN SUPPORT

Community
Videos
Quality & Reliability
Product Roadmaps

ABOUT US

Investors
Careers

CORPORATE HEADQUARTERS

Cypress Semiconductor Corp.
198 Champion Court
San Jose, CA 95134 USA
Tel: +1-408-943-2600

CUSTOMER SERVICE SUPPORT

+1-800-541-4736
Hours:
8:00AM - 5:00PM (local time)
Create a MyCase
Cypress Developer Community

INTERNATIONAL SUPPORT

+1-808-943-2600
United States +1-800-541-4736
Hours:
4:30AM - 1:30PM (pacific time)
7:30PM - 4:30AM (standard time)

OTHER REQUESTS

Contact Us
Report a Website Problem
Report a Security Vulnerability

