




SYMBOL DEFINITION			MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	12		
	LAST NO. USED	14		


DWG STATUS					ZONE	REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG							
05SE02	R	03	-	-		CLEARED REV COL, ADDED OPTIONAL LOGO & MATERIAL RECYCLING CODE NOTES AND MATERIAL SPEC WAS R0061354 PP BLK		230333	EOV	EOV	FR
21JN05	R	03	AA	-		2X R .300 +.006/-.010 WAS 2X R .300, 2X R .230 +.005/-.010 WAS 2X R .230 AND .200 +.009/-.005 WAS .200		269314	MDH	JAA	TP



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (.100)X(.010) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- RECOMMENDED HOLE SIZE FOR CLIP Ø .250 ±.010 HOLE IN .150 MAX THICK STOCK.
- THIS PART TO FIT .406 I.D. CONVOLUTED CONDUIT.
- (.100)X(.010) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.
- DIMENSIONS MARKED WITH A "▲" MAY VARY -.024 DUE TO BOW AND WITH A "*" +.024 DUE TO BOW.

DIMENSIONAL RANGE (IN)				CHART	H
FROM	0	>.750	>1.250	>2.750	>4.000
TO	.750	1.250	2.750	4.000	
TOLERANCE UNLESS OTHERWISE SPECIFIED					
±.005 ±.010 ±.012 ±.016 ±.020					
ANGULAR TOLERANCE ±2°					

DWG TYPE PART DRAWING	
STYLE	
VOLUME (CM³) 1.988	DISTR CODE D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 PERFECT FORM AT MMC1 DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
	

DELPHI												
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH												
DR							DATE					
APVD1 T. MUDREY							180C99					
APVD2 HUBBARD							14MR72					
APVD3 E. McDOWAN							24MR72					
APVD4												
APVD5												
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001												
MATERIAL M2097001 PP 1M BLK												
DRAWING NAME MOUN CLIP CDT 10MM ROSEBUD												
DRAWING NUMBER 08911497												
SIZE A1	SCALE 5:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1	STG R	REV 03	N/P AA						