





PED / NEG		FILE SPEC:	
		0396USER#00 DGN#SPECIFICATION0000000000000000 000000TIME#045000	
THERO ANGLE PROJECTION		 METRIC DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.	
			
CODE NO.	6900	TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ONE PLACE ± 0.3 TWO PLACE ± 0.15	ANGULAR ± "
O.C.			
DWG. DATE	15MY95	SCALE NONE	DR. RON BURNS 15MY95
EST. NO.		CK. RON BURNS	DATE 15MY95
REFERENCE NO.	1217145 R10 SIZE	APPR. A. HERRMANN	DATE 17MY95
		APPR.	DATE
MATERIAL SPEC M2279001 PA66 GF14 HS IM BLK			
NAME BASE FUSBLK MINI 56F			
PART NO.	1217 7145		SIZE 
PRODUCT INFORMATION DRAWING			



- NOTES -
1. THIS PART ACCEPTS 12092507 SECONDARY TERMINAL LOCK.
 2. THIS PART ACCEPTS 12092823 COVER OR EQUIVALENT.
 3. THIS PART ACCEPTS (2) 12077530 COVER CLIP OR EQUIVALENT
 4. THIS PART MATES WITH 12092327 MOUNTING BASE OR EQUIVALENT.
 5. MAX. INSULATION CRIMP MUST BE LESS THAN 4.75 HIGH AND 4.00 WIDE FOR ROWS A,B,C, & D - CAVITIES 3,5,7,9,11 & 13.
 6. MAX. INSULATION CRIMP MUST BE LESS THAN 6.30 HIGH AND 5.55 WIDE FOR ROWS A,B,C, & D - CAVITIES 1,2,4,6,8,10,12 & 14.
 7. THESE CAVITIES ACCEPT 12092556 TERMINAL OR EQUIVALENT:
ROWS A,B,C, & D - CAVITIES 1,3,5,7,9,11 & 13.
 8. THESE CAVITIES ACCEPT 12092525 TERMINAL BUS BAR OR EQUIVALENT:
ROWS A,B,C, & D - CAVITIES 2,4,6,8,10,12 & 14.
 9. SEALING CODE 0.
 10. MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
 11. (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

WARNING
GEOMETRY MAY NOT BE
DRAWN TO SCALE