



SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	6	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	6		

CWS STATUS				REVISION HISTORY				AUTH	DR	APVD	APVD
DATE	STG	REV	W/R	CHG	ZONE						
170C06	R	01	-	-		RELEASED		285783	SBH	JWG	SBH
02JA07	R	01	AA			REDRAWN TO PD		288253	SBH	JWG	SBH
100C09	R	02	-	-		ADD NOTE #5		409191	R.Z	JWG	E.Z
10JA11	R	02	AA	-		DIM #6 WAS 202.5		412974	WDZ	JWG	E.Z



- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
0.5° MAXIMUM DRAFT ANGLE
- MATERIAL RECYCLING CODE PER ISO 11469. (1)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON SURFACE AS SHOWN.
- (1)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON EXTERIOR SURFACE AS SHOWN, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
- 0.3MAX. RADIUS PERMISSABLE ON EDGES& FILLETS SHOWN AS SHARP.
- APPLICATE BUNDLE SIZE FROM Ø4mm TO Ø45mm, STRAP TO LOCK SLOT DISENGAGE FORCE MIN. 110 N.

DIMENSIONAL RANGE (MM)		TOLERANCE		CHART		IF	
FROM	TO	> 0	> 30	> 70	> 100	> 150	> 200
0	30	0.1	0.3	0.4	0.5	0.6	0.8
30	70	0.1	0.3	0.4	0.5	0.6	0.8
70	100	0.1	0.3	0.4	0.5	0.6	0.8
100	150	0.1	0.3	0.4	0.5	0.6	0.8
150	200	0.1	0.3	0.4	0.5	0.6	0.8
200	250	0.1	0.3	0.4	0.5	0.6	0.8
250	300	0.1	0.3	0.4	0.5	0.6	0.8
300	400	0.1	0.3	0.4	0.5	0.6	0.8
TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED	
1 ±0.1		1 ±0.3		1 ±0.4		1 ±0.5	
1 ±0.6		1 ±0.8		1 ±1		1 ±1.2	
ANGULAR TOLERANCE ±1°		ANGULAR TOLERANCE ±1°		ANGULAR TOLERANCE ±1°		ANGULAR TOLERANCE ±1°	

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (C/P)		DISTR CODE	
0.770		D	
UNLESS OTHERWISE SPECIFIED		THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE 2018 SUPPLEMENT TO Y14.5M-1994. SEPARATE PATTERNING OF FEATURES MAY BE DIMED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS		REFERENCE	
PROCESS SENSITIVE DIMENSION		THIRD ANGLE PROJECTION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		DO NOT SCALE	
		USE MATH DATA	

DELPHI		DELPHI PACKARD ELECTRIC SYSTEMS		WARREN, OH	
DR		DATE			
APV01 SUIBIN HUANG		170C06			
APV02 JIANWEI GUO		170C06			
APV03 SUIBIN HUANG		170C06			
APV04					
APV05					
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (09+000)					
MATERIAL M55Y2001 PLAS PA66 HS 1M BLK					
DRAWING NAME		MOUN STRAP			
DRAWING NUMBER		13608162			
SIZE A0		SCALE 2:1			
FRAME NO 1		SHEET NO 1 OF 1			
STG 02		REV AA			