






SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	79	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	20		

DWS STATUS				REVISION HISTORY		AUTH	DR	AP/D	AP/D
DATE	STG	REV	N/P	CHG	ZONE			1	2
28JUL03	R	01	-	-		RELEASED		243801	JAA JAA MLP
27AUG03	R	02	-	-		REMOVED RADIUS FROM CLIP SLOT		245155	BRB BRB MLP
18JUL06	R	02	AA	-		UPDATED PDM ATTRIBUTES		282056	EES EES MLP
16OCT06	R	02	AB			REVISED GRAPHICS		285096	JEC JEC MLP



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PA66< PER SAE J1344. (2.3)X(0.1) RAISED
CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 15448130
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CAVITIES A1,A2,A7,AB,B1,B2,B3,B4,B5,B6,B7,B8,B9,
B10,B11,B12,C1,C2,C3,C4,C5,C6,C7,C8,C9,C10,C11,C12,
D1,D2,D7 & D8 TO ACCEPT 15304701 TERMINAL OR EQUIVALENT.
MAX INSULATION CRIMP MUST BE LESS
THAN 3.15 HIGH AND 2.8 WIDE.
CAVITIES A3,A4,A5,A6,D3,D4,D5 & D6 TO ACCEPT 15304722 TERMINAL OR EQUIVALENT.
MAX INSULATION CRIMP MUST BE LESS
THAN 3.65 HIGH AND 4.2 WIDE.
SECONDARY TERMINAL LOCK 15304841 (TPA) SHOULD BE USED WITH WIRE GAUGE >12
SECONDARY TERMINAL LOCK 15359121 (TPA) SHOULD BE USED WITH WIRE GAUGE <=12
LEVER 15336387
- (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
- CONNECTOR HAS ABILITY TO PRE-STAGE MALE BLADE
STABILIZER 15401768
- TO BE USED WITH APPROPRIATE DELPHI PACKARD ELECTRIC SYSTEMS
DESIGNED HOLDERS.
- TO BE PROCESSED USING DELPHI PACKARD ELECTRIC SYSTEMS
BEST PRACTICE METHOD OR CUSTOMER ASSEMBLY INSTRUCTION.



DIMENSIONAL RANGE (MM)		SHORT ET	
FROM	> 0	> 30	> 100
TO	20	30	100
TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED	
[40,15] ±0.2		[40,15] ±0.2	
ANGULAR TOLERANCE 22°		ANGULAR TOLERANCE 22°	

DWS TYPE		PART DRAWING	
STYLE		DISTR CODE	D
VOLUME 10/1	18,135		
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS NOTED BY THE IN SCHEMA. DIMENSIONS OF FEATURES MAY BE BASED SEPARATELY REBARLESS OF DATUM REFERENCES.		ALL DIMENSIONS ARE IN MILLIMETERS	
THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA		UNIMATICS	

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
AP/D1 J.S. ALVARADO	28JUL03
AP/D2 J.S. ALVARADO	28JUL03
AP/D3 MATTHEW L. PENN	01AUG03
AP/D4	
AP/D5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
W3592012 PA66 HS 1M GRA LT	
DRAWING NAME: CONN 40 M GT 150 280	
DRAWING NUMBER: 15475870	
SIZE A0	SCALE 2:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 02
AB	AB