



SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		TOTAL NO OF INSPECTIONS REQUIRED	99
		LAST NO. USED	27


DWG STATUS				REVISION HISTORY				AUTH	DR	AP/D	AP/D
DATE	STG	REV	N/P	CHG							
31JAO5	R	48	-	-	CLEARED REV COL AND REDRAWN TO PD1 13516904, 13521471 & 13521475 - RELEASED				264071	ESH	JAA RWR
10JNO5	R	49	-	-	ALL PARTS - REVISED PLACES ON DIMS # 2, 5, 8, 11 & 17				269150	CCV	FRG RWR
21AP06	R	50	-	-	ALL PARTS - ADDED SECTION VIEW & MOVED DIM # 15				279872	ACG	JVM RWR




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN



NOTE:
NUMBER OF DIMENSIONS WILL VARY
DEPENDING ON CONNECTOR SIZE




VIEW A





TYPE 101

NOTE:
NUMBER OF DIMENSIONS WILL VARY
DEPENDING ON CONNECTOR SIZE




(1.6)X(0.2) RAISED
LETTERS AS SHOWN



VIEW SCALE DOES NOT REFLECT
ACTUAL PART SIZE

CORRECT MATERIAL RECYCLING CODE - SEE CHART



- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (2)X(0.2) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR - SEE CHART
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
SLC - SEE CHART
- (1.73)X(0.2) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
- DO NOT USE I, O, Q & U AS CAVITY LETTERS.

13516904	01	AB	28JAO5	-	M4629002 PBT GF20 BLK	105	16	15332180/ID405536	13516906	39.1	8.078
13521475	01	AB	28JAO5	-	M4629002 PBT GF20 BLK	104	14	15332172/ID405529	13521477	35.1	7.342
13521471	01	AB	28JAO5	-	M4629002 PBT GF20 BLK	102	8	15332148/ID405513	13521473	23.1	5.162
15332176/ID405535	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	105	16	15332180/ID405536	15332181/ID405539	39.1	8.077
15332168/ID405528	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	104	14	15332172/ID405529	15332173/ID405532	35.1	7.340
15459921	01	AB	06MY03	-	M4629002 PBT GF20 BLK	103	12	15332164/ID405521	15459922	31.1	6.605
15332160/ID405520	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	103	12	15332164/ID405521	15332165/ID405525	31.1	6.604
15332144/ID405512	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	102	8	15332148/ID405513	15332149/ID405517	23.1	5.161
15459950	01	AB	06MY03	-	M4629002 PBT GF20 BLK	101	10	15332156/ID405303	15459949	27.1	5.868
15332152/ID405302	33	AB	05AU99	-	M3571002 PA6 GB20+GF10 HS BLK	101	10	15332156/ID405303	15332157/ID405305	27.1	5.867
PART NO	REV	N/P	DATE	STATUS	MATERIAL SPECIFICATION AND COLOR	TYPE	CAVITIES	SLC	MATING CONNECTOR	A	VOL CM³

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED	
FROM	TO	±	±
0	20	±0.2	±0.3
20	30	±0.3	±0.4
30	70	±0.4	±0.5
70	100	±0.5	±0.6
100	150	±0.6	±0.8
150	200	±0.8	±1.0
200	250	±1.0	±1.2
250	300	±1.2	±1.5
300	400	±1.5	±2.0

DWG TYPE		PART DRAWING	
STYLE	SEE CHART	DISTR CODE	D
VOLUME (QTY)	SEE CHART	UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE IN-SITU DIMENSIONING PRACTICE. UNLESS OTHERWISE SPECIFIED, SEPARATE MATING OF FEATURES MAY BE BASED SEPARATELY PER DELPHI 1044001.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION			
DO NOT SCALE USE MATH DATA			

DELPHI		DELPHI PACKARD ELECTRIC SYSTEMS	
WARR, OH			
DR		DATE	
AP/D1 K/ENG		155E98	
AP/D2 R. KOCH		155E98	
AP/D3 R. WIS.		185E98	
AP/D4			
AP/D5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 1044001			
MATERIAL SEE CHART			
DRAWING NAME			
TAXI CONN F GT ISO			
DRAWING NUMBER			
15326979			
SIZE	SCALE	FRAME NO	SHEET NO
A0	5:1	1 OF 1	1 OF 1
		REV	N/P
		R	50