




SYMBOL DEFINITION		MISSING SYMBOLS
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	
	24	
	LAST NO. USED	17

CWS STATUS		ZONE		REVISION HISTORY		AUTH		DR		APVD	
DATE	STG	REV	N/P	CHG							
10AP17	R	01	-	-	ALL PARTS - RELEASED PART DRAWING	436283	KYT	KYT	BVC		
16MY17	R	02	-	-	ALL PARTS - UPDATED PART AVAILABILITY	436694	DAG	DAG	BVC		
27JUL17	R	03	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	437256	JVM	JVM	BVC		





(2X 2) 2X 0.42 +0.02 -0.13
APPLIES TO BOTH SIDES OF STATIONARY CONTACT FROM TOP OF CONTACT BUMPS

(3X 8) 3X 3.05 +0.05 TYP
MUST BE MAINTAINED FOR ENTIRE 8.6mm TERMINAL BOX LENGTH


(2X 7) 2X 3.75 +0.1 -0.06 TYP

(3) 4.05 +0.1 -0.05
MUST BE MAINTAINED FOR ENTIRE 8.6mm TERMINAL BOX LENGTH



SCALE 20:1



SECTION B-B



SECTION C-C



SECTION K-K

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
RECOMMENDED MATING BLADE THICKNESS 0.8 +0.04/-0.03mm
RECOMMENDED MATING BLADE WIDTH NOT TO EXCEED 2.9mm AND NO LESS THAN 2.4mm. SEE USCAR-2001 DRAWING (2.8 BLADE) FOR OTHER MATING BLADE REQUIREMENTS.
DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
MAXIMUM CURRENT CAPACITY AS DEFINED BY USCAR-2 R5 SECTION 5.3.3 IS 35 AMPS WITH 5.0 mm² COPPER CABLE.
* DENOTES DIMENSIONS MADE AT CUT-OFF AND CRIMP DIE
PLUS ANGLE IS WING BOTTOM SURFACE ROTATED COUNTERCLOCKWISE AGAINST THE BOX BOTTOM SURFACE.
PLATING TYPE:
1. REFLOW TIN 1.9 - 3.3 MICROMETERS THICK OVER NICKEL UNDERPLATE 0.13 - 0.5 MICROMETERS THICK.
PLATING TYPE INFORMATION SHOWN ABOVE IS FOR REFERENCE ONLY; PLATING REQUIREMENTS ARE CONTAINED IN APPLICABLE MATERIAL SPECIFICATIONS.
 - PARTS MEET THE PERFORMANCE REQUIREMENTS OF GMW3191 DEC 2007 AND SAE/USCAR-2 R5 REVISIONS FOR THE FOLLOWING CLASSIFICATIONS:
TEMPERATURE CLASS 3 (-40°C TO +125°C)
VIBRATION CLASS 1 (ON BODY OR CHASSIS)
SEALING CLASS 1 (UNSEALED).

PROCESS SENSITIVE DIMENSION	
FROM 0 TO 12	CHART C
TOLERANCE UNLESS OTHERWISE SPECIFIED	
10.1	10.2
ANGULAR TOLERANCE 12°	

THIRD ANGLE PROJECTION	
DO NOT SCALE	USE MATH DATA

DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WARREN, OH
COPYRIGHT 2017 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DR	DATE
APV01 YAMIR TELLEZ	07AP17
APV02 YAMIR TELLEZ	07AP17
APV03 GREG V. CHURLEY	07AP17
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (0944990)	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI TERM F OCS 2.8 SN	