



5 ALL THE SEALED CONNECTOR APPLICATIONS MUST BE USED WITH CHRYSLER WIRE SPEC. MS-8288, MS-9502 OR ISO 6722 EQUIVALENTS THIN WALL X-LINK ONLY
 A- ASSEMBLIES WITH FCI P/N'S 54200239 OR 54200240 END SEALS MUST BE USED WITH 20 TO 0.14WG OR ISO EQUIVALENTS WIRES WITH INSULATION 0.170 TO 0.277 O.D.
 B- ASSEMBLIES WITH FCI P/N'S 54200241 OR F480510 END SEALS MUST BE USED WITH 14 TO 10AWG OR ISO EQUIVALENTS WIRES WITH INSULATION 0.250 TO 0.409 O.D.

6 ALL NON-SEALED APPLICATIONS MAY BE USED WITH ANY WIRE INSULATION 22 TO 10AWG OR ISO EQUIVALENTS (EXCEPT AS NOTED BELOW) PROVIDED THAT A TERMINAL GRIP FOR THAT CORE/INSULATION IS SHOWN ON C15005-CUST MALE TERMINAL DRAWING

NOTE: MAX. INSULATION CRIMP WIDTH = 4.50
 MAX. INSULATION CRIMP HEIGHT = 4.50
 MAX. INSULATION CRIMP DIA. = 4.09 (10 GA THIN WALL)

8623 211 403 8