






SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	LAST NO. USED	NO MISSING SYMBOL NUMBER	
	38	22		

CWS STATUS				REVISION HISTORY				AUTH		DR		APV/D	
DATE	STG	REV	N/P	CHG	ZONE								
10FE00	R	001	-	-		CLEARED REV COLUMN: 15359163 - RELEASED		000005	JHN	PHC	MDM		
08MY00	R	002	-	-		15359163 - TERMINAL FORM ID 21 WAS ID 19		200183	FRG	MVA	MDM		
30JN00	R	003	-	-		15359163 - REV MAT'L SPEC		202037	TLPT	TLPT	MJD		
15JN05	R	04	-	-		CORRECTED DIM LOCATION FOR DIM 2.6		269209	MJM	MJM	MKM		
08DE06	R	05	-	-		REVISED MATERIAL SPEC-12191888,12191887 12077628,12045773 WAS P3607402 AND 12077150 WAS PM003636		287631	MM	MM	MKM		
23NO07	R	06	-	-		13654490 - RELEASED		402515	EFS	JVM	ACB		
25MR08	R	07	-	-		ALL ACTIVE PARTS DIM 2X 4 MAX EXCLUDING COIN WAS 2X 3.6 +/- 0.15		404175	ARV	PYP	ARV		
22JA09	R	08	-	-		ALL ACTIVE PARTS - DIM 2.5 +/- .15 WAS +/- .10, ADDED NOTE TO DIM 2.5 +/- .15 & UPDATED MAT'L CALLOUT		407116	CBG	SCR	BEM		
31JL12	R	09	-	-		12045773, 12077628, 12191887 & 12191888 - UPDATED PDM ATTRIBUTES		419104	JGM	JGM	MAA		
07AU12	R	10	-	-		13654490, 15359163 AND 12177150 UPDATED MAT'L CALLOUT		419193	DCH	JVM	MAA		



TYPE 102

SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
TERMINAL 12048074
- PART TO BE USED WITH CABLE SEAL

12092703	B2	-	0.381 X 35.71	COPPER ALLOY	12077628	C5	-	COPPER ALLOY	0.35 - 0.5	21	2.4 - 1.47	101	5.9	2.4	2.55	2.1	4.7
12092668	C2	-	0.381 X 35.71	COPPER ALLOY	12045773	H5	-	COPPER ALLOY	0.35 - 0.5	22	1.63 - 1.47	102	5.9	2.2	2.6	1.9	4.7
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SPEC	SIZE (MM²)	ID	DIA	TYPE	F	G	N	R	P
UNPLATED					PLATED					CABLE							

PROCESS SENSITIVE DIMENSION				THIRD ANGLE PROJECTION		DO NOT SCALE	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	CHART	CD					
FROM 0 TO 12	0	> 12					
TOLERANCE UNLESS OTHERWISE SPECIFIED	±0.1	±0.2					
ANGULAR TOLERANCE	±2°						

DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH COPYRIGHT 1996 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS CONVICTION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.						
OR APV01 L. R. MOYSEN M APV02 W. TURNBULL APV03 C. SCHAEFER APV04 APV05	DATE 04SE96 07SE96 18OC96					
SUBSTANCES OF CONCERN AND RECYCLED CONTENT, PER DELPHI (0944900)						
DRAWING NAME TAXI TERM M M/P 150 SEALED						
DRAWING NUMBER 12089630						
SIZE A0	SCALE 10:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1	STG R	REV 10	N/P