








PART NO	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC (PLATING)	SIZE (MM²)	ID	CABLE	DIA	B ₁ ± 0.2	B ₂ +0.35 -0.3	(H ₁)	(H ₂)
13576051	01	-		0.1778 X 30.48	M-1628-924 (TIN)	0.22	24	1.1-1.3	1.4	1.7	1.5	1.6	
15359541	02	AF		0.1778 X 30.48	M-3696-FN1 (GOLD)	0.5-0.8	19	1.9-1.64	2.08	2.5	2.4	2.5	
15401440	03	AK		0.1778 X 30.48	M-1628-924 (TIN)	0.5-0.8	19	1.9-1.64	2.08	2.5	2.4	2.5	
15394147	03	AJ		0.1778 X 30.48	M-1628-924 (TIN)	0.35	22	1.63-1.47	1.65	2.1	1.9	2.4	
15356827	04	AG		0.1778 X 30.48	M-3696-DN2 (GOLD)	0.5-0.8	19	1.9-1.64 SEE NOTE #4	2.08	2.5	2.4	2.5	
15356826	04	AG		0.1778 X 30.48	M-3696-DN2 (GOLD)	0.35	22	1.63-1.47	1.65	2.1	1.9	2.4	



SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	27	NO MISSING SYMBOL NUMBER
	LAST NO. USED		
		19	



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MAXIMUM CURRENT CAPACITY IS 7 AMPS.
 - MATING COMPONENTS: CONNECTOR 15356814 OR EQUIVALENT PIN (SEE MATING PIN DESIGN VIEWS)
 - TERMINAL 15356827 MAY BE USED WITH 0.5 mm² CABLE UP TO 2.19 MAX O.D. THIS IS A SPECIAL APPLICATION WHERE CONNECTOR CAVITIES ARE AT 3.0 MIN NOMINAL SPACING (REFERENCE CONNECTOR ASSEMBLY PE123151 OR EQUIVALENT)

DWG STATUS		ZONE		REVISION HISTORY		AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG					
03MY00	R	001	-	-	ALL PARTS- RELEASED	000005	LOA	PHC	KG
19SE00	R	002	-	-	15394147 & 15401440 - RELEASED	000005	JMR	JMR	BTG
06N000	R	003	-	-	ALL PARTS REVISED. 15359541 - RELEASED REVISED MATING PIN DESIGNS.	204501	SHH	SHH	KG
18JA01	R	004	-	-	15394147 & 15401440 - MAT'L SPEC WAS M-1628	206006	TLD	TLD	BTG
23JA01	R	005	-	-	ALL PARTS - REVISED TOLERANCES, ADDED ALTERNATE CONSTRUCTION VIEW	206205	CJP	CJP	KG
23JA01	R	006	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES, REVISED GRAPHICS	206881	CJP	CJP	KG
30AP01	R	007	-	-	ALL PARTS: REVISED MAT'L SPEC IN CHART, (1.7) WAS 1.7 MIN	209072	JMR	JMR	KG
28SE01	R	008	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	215149	AMG	AMG	KG
24JL02	R	09	-	-	ALL PARTS - ADDED NOTE: REVISED GRAPHICS TO SHOW ROUND CRIMP	228371	MAC	MAC	KG
31JA03	R	10	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	231297	JVM	JVM	KG
23JA03	R	11	-	-	ALL PARTS - ADVANCED REVISION LEVEL	235918	LMB	LMB	TV
30JA04	R	12	-	-	15394147, 15401440 - REVISED CUSTOMER PRINT	250730	JEB	JEB	TV
04MR04	R	13	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES; 15394147, 15401440 - REVISED CUSTOMER PRINT WAS REVISED CUSTOMER PRINT	252450	ADK	ADK	KG
01JL04	R	14	-	-	ALL PARTS - ADDED PIN TIP FLAT REQUIREMENT, NOTE #13, AND GAGE NUMBER.	256626	MJM	MJM	KG
14JA05	R	15	-	-	ALL PARTS - UPDATED FORMAT 15401440 - UPDATED PDM ATTRIBUTES	263237	BRB	BRB	KG
01DE05	R	16	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	274991	TS	TS	JS
02MR06	R	17	-	-	13576051 - RELEASED AND ALL PARTS - UPDATED PDM ATTRIBUTES	277466	JS	JS	KG
06FE07	R	18	-	-	15401440 - UPDATED PDM ATTRIBUTES	400433	JBD	AUG	EJH

3					2					1				
DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2				
DATE	STG	REV	N/P	CHG										
03MY00	R	001	-	-	ALL PARTS- RELEASED	000005	LOA	PHC	KG					
19SE00	R	002	-	-	15394147 & 15401440 - RELEASED	000005	JMR	JMR	BTG		H			
06N000	R	003	-	-	ALL PARTS REVISED. 15359541 - RELEASED REVISED MATING PIN DESIGNS.	204501	SHH	SHH	KG					
18JA01	R	004	-	-	15394147 & 15401440 - MAT'L SPEC WAS M-162B	206006	TLD	TLD	BTG					
23JA01	R	005	-	-	ALL PARTS - REVISED TOLERANCES, ADDED ALTERNATE CONSTRUCTION VIEW	206205	CJP	CJP	KG					
23JA01	R	006	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES, REVISED GRAPHICS	2068B1	CJP	CJP	KG					
30AP01	R	007	-	-	ALL PARTS; REVISED MAT'L SPEC IN CHART, (1.7) WAS 1.7 MIN	209072	JMR	JMR	KG					
28SE01	R	008	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	215149	AMG	AMG	KG		O			
24JL02	R	09	-	-	ALL PARTS - ADDED NOTE; REVISED GRAPHICS TO SHOW ROUND CRIMP	22B371	MAC	MAC	KG					
31JA03	R	10	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	231297	JVM	JVM	KG					
23JA03	R	11	-	-	ALL PARTS - ADVANCED REVISION LEVEL	235918	LMB	LMB	TV					
30JA04	R	12	-	-	15394147, 15401440 - REVISED CUSTOMER PRINT	250730	JEB	JEB	TV					
04MR04	R	13	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES; 15394147, 15401440 - REVISED CUSTOMER PRINT WAS REVISED CUSTOMER PRINT	252450	ADK	ADK	KG					
01JL04	R	14	-	-	ALL PARTS - ADDED PIN TIP FLAT REQUIRE- MENT, NOTE #13, AND GAUGE NUMBER.	256626	MJM	MJM	KG					
14JA05	R	15	-	-	ALL PARTS - UPDATED FORMAT 15401440 - UPDATED PDM ATTRIBUTES	263237	BRB	BRB	KG		F			
01DE05	R	16	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	274991	TS	TS	JS					
02MR06	R	17	-	-	13576051 - RELEASED AND ALL PARTS - UPDATED PDM ATTRIBUTES	277466	JS	JS	KG					
06FE07	R	18	-	-	15401440 - UPDATED PDM ATTRIBUTES	400433	JBD	AUG	EJH					

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)	DISTR CODE	D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 94A GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE BAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION	DO NOT SCALE		
	USE MATH DATA		

DELPHI					
DELPHI PACKARD ELECTRIC SYSTEMS					
WARREN, OH					
DR			DATE		
APVD1			LUIS ORDUNA A.		
APVD2			P. H. CASTRILLON		
APVD3			K. GRZENA		
APVD4					
APVD5					
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001					
MATERIAL SEE CHART					
DRAWING NAME					
TAXI TERM F MICRO 64					
DRAWING NUMBER					
15356828					
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV
A1	10:1	1 OF 1	1 OF 2	R	18

3	2	1
---	---	---