








DARGESTELLT IST MVL P/N: 6 011 07 41/44
PICTURED DELPHI P/N: 10756353/33512923

6 011 07 14	33500681	A3	1-3µm Sn ALLSEITIG / ALL SIDES
6 011 07 34	33500682	A2	MIN. 0.8µm AuCo 0.3 UEBER / OVER 1.3-2µm Ni
6 011 07 44	33512923	A1	0.5µm Ni ALLSEITIG / ALL SIDES
6 011 07 12	33500680	A2	2-4µm Ag PASSIVIERT/PASSIVATED ALLSEITIG / ALL SIDES
6 011 07 32	33505427	A1	1.5µm Ag PASSIVIERT/PASSIVATED ALLSEITIG / ALL SIDES
6 011 07 42	33500683	A1	1-3µm Sn FEUERVERZINNT/HOT TIN
6 011 07 11	10756351	A1	1-3µm Sn FEUERVERZINNT/HOT TIN
6 011 07 31	10756352	A1	1-3µm Sn FEUERVERZINNT/HOT TIN
6 011 07 41	10756353	A1	1-3µm Sn FEUERVERZINNT/HOT TIN
MVL TEILE-NR. PART NO.	DELPHI TEILE-NR. PART NO.	MASS DIMENSION	OBERFLAECHE SURFACE FINISH

6 011 07 44	33512923	0.8µm Au	>1.0-2.5	000	3.6	3.8	0.9	5.3	5.0	1.75	3.3	6.8	0.8	CuSn4 R480	6 099 40 23	10779159	2.0-2.7	ROT-BRAUN AUBURN	
6 011 07 42	33500683	2-4µm Ag												CuFe2P R420	ODER / OR	ODER / OR			
6 011 07 41	10756353	1-3µm Sn												CuFe2P R420	6 099 40 34	10779161			2.7-2.9
6 011 07 34	33500682	0.8µm Au	0.5-1.0	00	2.5	2.7	0.6	5.1	4.8	1.65	3.0	6.3	0.7	CuSn4 R480	6 099 40 15	10779162	1.2-2.0	BLAU BLUE	
6 011 07 32	33505427	2-4µm Ag												CuFe2P R420					
6 011 07 31	10756352	1-3µm Sn												CuFe2P R420					
6 011 07 14	33500681	0.8µm Au	>0.20-0.35	0	2.1	2.1	0.4	4.7	4.5	1.6	2.5	6.3	0.7	CuSn4 R480					
6 011 07 12	33500680	2-4µm Ag												CuFe2P R420					
6 011 07 11	10756351	1-3µm Sn												CuFe2P R420					
MVL TEILE-NR. PART NO.	DELPHI TEILE-NR. PART NO.	OBERFLÄCHE SURFACE FINISH	CRIMPGRÖSSE CRIMP SIZE (mm ²)	CRIMP- CODE	B1 ±0.3	(H1) ±0.2	R1 ±0.2	B2 (H2) ±0.3	R2 ±0.2	E1 ±0.2	F ±0.5	G ±0.2	GRUNDKÖRPER CONTACT BODY	MVL ART.-NR. ART.-NO.	DELPHI ART.-NR. ART.-NO.	ISOLATION-Ø INSULATION	FARBE COLOR		
MATERIAL														EINZELADERDICHUNG/SINGLE WIRE SEAL					



14-10262	23.01.15	D	ABII,AB7	DELPHI P/N ADDED	Nethaj	Schneider	Moerntein
918/06	10.12.08	C05	-	Hinzu: Hinweis Nr. 4			
432/07	14.08.07	C04	-	ERSTELLUNG IN PRO-E			
ECN-NR. ECN NUMBER	DATE DATUM	REVISION INDEX	POSITION POSITION	CHANGE DESCRIPTION ÄNDERUNG	DRAWN BY GEZ.	CHK. BY GEPR.	APPR. BY GEW.
PRODUCT SPEC. PRODUCT SPECIFIK.	PACKAGING SPEC. VERPACKUNGS SPECIFIK.	APPLICATION SPEC. ANWENDUNGS SPECIFIK.	COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.	DELPHI CORPORATION NÜRNBERG GERMANY			
TOLERANCES DIN 2768-fm TOLERANZEN DIN ISO 1101 COUNTERPART N°. MASSE <0.5: ±0.05	MATERIAL MATERIAL SEE TABLE	SURFACE FINISH OBERFLÄCHE SEE TABLE	COLOUR FARBE ---	DELPHI CORPORATION NÜRNBERG GERMANY			
DO NOT SCALE DRAWING ZEICHNUNG NICHT VERMESSEN	DATE DATUM 14.08.07	NAME NAME S. Weiss	TITLE BENENNUNG FLACHSTECKER 2.8 - DCS2 ANWENDUNG MIT EAA MALE TERMINAL 2.8 - DCS2 APPLICATION WITH SWS	ECO Loc. Code STANDORT CODE GN	DRAWING NUMBER ZEICHN. NUMBER 6 011 07 11 - 44	DWG SIZE FORMAT A2	SHEET BLATT 1 von 1
CHECKED BY GEPR. 14.08.07	APPROVED BY GEW. 14.08.07	ESR NO. ESR NUMBER ---	CAT. NO. KATALOG NR. ---	FILE NAME DATE/ NAME 60110711C.C05	SCALE MASSSTAB 5:1		