





THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER
ORIGINAL

①



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES
2011/65/EU FOR ROHS COMPLIANCY.

- SPECIFICATIONS:**
1. INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0, COLOR: (GREEN)
 2. CONTACT MATERIAL: COPPER ALLOY
 3. CONTACT PLATING: 15 MICROINCHES OF GOLD ON CONTACT AREA, TIN ON CONTACT TAIL, NICKEL UNDERPLATE.
 4. CURRENT RATING: 3A CONTINUOUS
 5. 2A CONTINUOUS @ 100°C AMBIENT TEMPERATURE
 6. CONTACT RESISTANCE: 10 MILLIOHMS MAX
 7. DIELECTRIC WITHSTANDING VOLTAGE: 1800 VAC rms, AT SEA LEVEL, BETWEEN ADJACENT CONTACTS.
 8. INSULATION RESISTANCE: 5000 MEGOHMS MINIMUM.
 9. OPERATING TEMPERATURE: -65°C TO +125°C
 10. INSERTION FORCE: 16oz MAX. PER CONTACT WHEN TESTED WITH A .0700" THICK GAUGE.
 11. WITHDRAWAL FORCE: 1oz MINIMUM PER CONTACT WHEN TESTED WITH A .0620" THICK GAUGE.

337 CARD EDGE CONNECTOR



EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. 337-044-521-300

DRAWN: R.STA.MONICA DATE: OCT.03/2014

PART NUMBER

337-044-521-300

DRAWING NUMBER

337-044-521-300

ISSUE

1