






AWG 2026

Drahtcrimp
bare wire crimp section
Schnitt B-B
cross section B-B
M 10:1
Toleranz ± 0.15
tolerance ± 0.15



Isoliercrimp
insulation crimp area
Schnitt A-A
cross section A-A
M 10:1
Toleranz ± 0.15
tolerance ± 0.15



Anforderungsstufe / <i>grade</i>	107	=	1.2 μm Au
Anforderungsstufe / <i>grade</i>	207	=	0.8 μm Au
Anforderungsstufe / <i>grade</i>	2057	=	0.5 μm Au

Consider protection memo from DIN 34

All rights reserved.
Only for information.
To insure that this is the latest
version of this drawing, please
contact one of the ERNI companies
before using.

Subject to modification without
prior notice.
Drawing will not be updated.

www.ERNI.com

V:00054817 S7A

TMC-Kontaktstift Crimp
TMC male contact Crimp

014342

TMCKOS

1